

SPECIFICATION CONTROL DRAWING

44AM316+

Title

SIX CONDUCTOR CABLE, SHIELDED, GENERAL PURPOSE, 600 VOLT

Date

1-10-06


Revision

A

This specification sheet forms a part of the latest issue of Raychem Specification 44 and NEMA WC 27500 as applicable.

COMPONENT WIRES – 44A011+

SHIELD – COPPER, COATING SAME AS ON CONDUCTOR EXCEPT TIN-COATED SHIELD WITH SILVER-COATED HIGH STRENGTH ALLOY CONDUCTOR



FILAMENT BINDER AS REQUIRED

CABLE CONSTRUCTION DETAILS

PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	OUTSIDE DIAMETER (in.)		MAXIMUM WEIGHT (lb/1000 ft)
			NOMINAL	MAXIMUM	
44AM316+-26-*	26	38	.119	.126	14.1
44AM316+-24-*	24	38	.137	.144	19.2
44AM316+-22-*	22	38	.158	.165	26.3
44AM316+-20-*	20	38	.182	.189	36.6
44AM316+-18-*	18	38	.212	.219	52.7
44AM316+-16-*	16	38	.233	.243	65.4
44AM316+-14-*	14	36	.288	.301	102.
44AM316+-12-*	12	36	.345	.358	153.

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature
VOLTAGE RATING: 600 volts (rms) at sea level
DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz,
 15 seconds (minimum), 30 seconds (maximum)
SHIELD COVERAGE: 85% (minimum)

PART NUMBER:

The "+" in the part numbers above shall be replaced by the applicable conductor material designator as follows:

- 1 tin-coated copper
- 2 silver-coated copper
- 3 nickel-coated copper
- 4 silver-coated high strength copper alloy (awg's 26-16 only)
- 6 nickel-coated high strength copper alloy (awg's 26-20 only)

The "*" in the part numbers above shall be replaced by color code designators with a slash separating component wire colors. Colors shown do not necessarily reflect the sequence of manufacturing.

1/ Example: AWG 20, tin-coated copper wires; black, brown, red, orange, yellow and green: 44AM3161-20-0/1/2/3/4/5

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.

Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable
 501 Oaks Avenue
 Redwood City, CA 94063-3800
 Phone: 1-800-227-8816
 Fax: 1-650-361-6297