

# SPECIFICATION CONTROL DRAWING

**44B413X**

TITLE

THREE CONDUCTOR CABLE, JACKETED, GENERAL PURPOSE, 600 VOLT

Date


1-14-07

Revision

B

This specification sheet forms a part of the latest issue of Raychem Specification 55A.

COMPONENT WIRES - 44A011X

JACKET - RADIATION-CROSSLINKED,  
MODIFIED ETFE

## CABLE CONSTRUCTION DETAILS

PART NUMBER 1/	CONDUCTOR SIZE (AWG)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)		MAXIMUM WEIGHT (lbs/1000 ft.)
		MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
44B413X-26-*	26	.006	.008	.089	.094	6.1
44B413X-24-*	24	.006	.008	.102	.108	8.6
44B413X-22-*	22	.006	.008	.118	.123	12.0
44B413X-20-*	20	.006	.008	.135	.142	16.9
44B413X-18-*	18	.006	.008	.156	.164	24.8
44B413X-16-*	16	.006	.008	.172	.180	30.9
44B413X-14-*	14	.006	.008	.208	.219	47.0
44B413X-12-*	12	.007	.009	.251	.264	72.5

## CABLE RATINGS AND ADDITIONAL REQUIREMENTS

### TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

ACCELERATED AGING: 300 ± 3°C for 7 hours

BLOCKING: 150 ± 3°C for 6 hours

DIELECTRIC WITHSTAND: 2500 volts (rms), 60 Hz, 1 minute

FLAMMABILITY: 3 seconds (maximum);

3 in. (maximum); no flaming of facial tissue

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in<sup>2</sup> (minimum)

LIFE CYCLE: 200 ± 3°C for 168 hours

LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

### PART NUMBER:

The " X " in the part numbers above shall be replaced by the applicable conductor material designator as follows:

- 1 tin-coated copper
- 2 silver-coated copper
- 3 nickel-coated copper
- 4 silver-coated high strength copper alloy (AWG's 26-16 only)
- 6 nickel-coated high strength copper alloy (AWG's 26-20 only)

The "\*\*\*" in the part numbers above shall be replaced by color code designators with a slash separating component wire colors and a dash separating the component wire colors from the jacket color. Colors shown do not necessarily reflect the sequence of manufacturing.

1/ Example: AWG 12, tin-coated copper, black, brown and red component wires; white jacket:  
44B4131-12-0/1/2-9

NOTE: Nominal values are for information only.  
Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.  
Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx"). OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.  
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

**tyco**  
Electronics

**Raychem** Wire & Cable  
501 Oakside Avenue  
Redwood City, CA 94063-3800  
Phone: 1-800-227-8816  
Fax: 1-650-361-6297