





CONSTRUCTION OPTION 1




CONSTRUCTION OPTION 2

CONSTRUCTION OPTION 3

DETAIL A
OPTIONAL CONSTRUCTIONS



RECOMMENDED PANEL CUTOUT



REVISIONS				
P.	LTN	DESCRIPTION	DATE	APVD
AG9		REDRAWN PER ECO-19-005708	02MAY2019	BKW SF

1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOCK™ PLUG
2. RECOMMENDED PANEL THICKNESS 0.76 - 2.29.
3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
4. OPTIONAL FOR KEYING HOUSING IN PANEL.
5. CIRCUIT NUMBER 1 LOCATION.
6. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
7. FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
8. UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
9. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINIS!
10. CONSTRUCTION OPTION 1 ONLY ALLOWED
CONSTRUCTION OPTIONS 2 AND 3 NOT PERMISSIBLE
11. PREPRODUCTION-FASR REQUIRED
12. MATERIAL: PA66, UL94 V-0, GWIT 775°C
13. TRADEMARK LOCATION: AMP OR TE

12	NATURAL	13-480699-0
10	NATURAL	2-480699-0
	BLACK	1-480699-9
	GRAY	1-480699-8
	BLUE	1-480699-6
	GREEN	1-480699-5
9	SUPERSEDED BY 1-480699-0	YELLOW
	ORANGE	1-480699-3
9	OBSOLETE	RED
	BROWN	1-480699-1
	NATURAL	1-480699-0
	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	0 PLC ±	1 PLC ±	2 PLC ±0.13	3 PLC ±	4 PLC ±	ANGLES ±1°
mm							

DWN	B. WEAVER	02MAY2019
CHK	S. FERNANDES	02MAY2019
APVD	T. BENCHOFF	02MAY2019

NAME: CAP, 2 CIRCUIT UNIVERSAL MATE-N-LOCK

SIZE: A | CAGE CODE: 00779 | DRAWING NO: 480699

MATERIAL: NYLON UL94V-2

CUSTOMER DRAWING

SCALE: 4:1 | SHEET: 1 OF 1 | REV: AG9