




D



1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.

2. RECOMMENDED PANEL THICKNESS 0.76 – 2.29.

3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.

4 OPTIONAL FOR KEYING HOUSING IN PANEL.

5 CIRCUIT NUMBER 1 LOCATION.




6. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.

7 FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.

8 UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.


9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

C



RECOMMENDED PANEL CUT OUT

B



3-DIMENSIONAL MODEL
NTS

6.35	.250	—	—
4.45	.175	27.43	1.080
2.79	.110	26.43	1.041
2.54	.100	25.91	1.020
2.29	.090	20.70	.815
0.76	.030	20.32	.800
0.38	.015	12.19	.480
0.25	.010	8.13	.320
0.13	.005	6.99	.275
MM	IN	MM	IN

CONVERSION TABLE






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
AN		REVISED PER ECR-25-231608	24MAR2025	AK	BR

9 OBSOLETE SUPERSEDED BY 1-480707-0	BLACK	1-480707-9
	GRAY	1-480707-8
	BLUE	1-480707-6
	GREEN	1-480707-5
	YELLOW	1-480707-4
	ORANGE	1-480707-3
	RED	1-480707-2
	BROWN	1-480707-1
	NATURAL	1-480707-0
COLOR		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 29JUL04	 TE Connectivity Ltd.				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± — 1. PLC ± — 2. PLC ± 0.13 3. PLC ± — 4. PLC ± — ANGLES ± 0°30' FINISH —	CHK S. RIDGILL 29JUL04					
		APVD S. RIDGILL 29JUL04					
		PRODUCT SPEC					
APPLICATION SPEC		NAME CAP, 9 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)					
MATERIAL NYLON, UL94V-2		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
		A1		00779	C480707	—	
		CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 2	REV AN

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

1. MOLD NUMBERS APPROXIMATELY 3mm HIGH AT WIRE END OF HOUSING (12 POINT DAVID TYPE);CLARIFICATION MARKS UNDER THE 6 & 9.
2. CHARACTERS TO BE MOLDED ON HOUSING IN A MANNER AS TO BE READ FROM WIRE END ONLY.



5.08	.200	—	—
4.70	.185	27.43	1.080
3.18	.125	25.91	1.020
0.38	.015	20.70	.815
0.25	.010	20.32	.800
0.13	.005	8.13	.320
MM	IN	MM	IN

CONVERSION TABLE

4805 (1/15)

SUPERSEDED BY 1-480707-0

NATURAL

2-480707-0

COLOR

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER	29JUL04	TE Connectivity Ltd.	
		CHK S. RIDGILL	29JUL04		
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S. RIDGILL	29JUL04	NAME	CAP, 9 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)
mm	0. PLC ± — 1. PLC ± — 2. PLC ± 0.13 3. PLC ± — 4. PLC ± — ANGLES ± 0°30'	PRODUCT SPEC	—	SIZE	CAGE CODE
	FINISH —	APPLICATION SPEC	—	DRAWING NO	RESTRICTED TO
MATERIAL NYLON, UL94V-2		WEIGHT	—	A100779	—
CUSTOMER DRAWING			SCALE	4:1	SHEET 2 OF 2
			REV AN		