






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	27NOV2023	NK	JDB
	A2	DRAWING RE-CREATED IN CREO	27DEC2023	NK	JDB

SECTION A-A



INSPECTION LEVEL 1: CONTROL CHART REQUIRED
1/1 PROOF OF PROCESS CAPABILITY OR 100% TEST IF
PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
2/2 PROOF OF MEAN VALUE, STANDARD DEVIATION AND
MACHINE CAPABILITY

3/3 PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

1 PART; 100 PCS. IN BUBBLE BAGS/BULK

1	4	-	494098-E	PINS	2
	1	-	494096-E	HOUSING	1
494094-E	REV	PART NO.	DESCRIPTION	ITEM NO.	
-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)				
QTY	PARTS LIST				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B S ADRUSH 20SEP2023	 TE Connectivity		
DIMENSIONS: mm		CHK M SZELAG 22SEP2023			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mH ISO 8015		APVD J DE BRUJN 22SEP2023	NAME M12 FEMALE/MALE ADAPTER, A CODE, 4P		
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		PRODUCT SPEC 108-94887	-		
MATERIAL		APPLICATION SPEC 114-94781	SIZE A3		
-		WEIGHT -	CAGE CODE 00779		
-		CUSTOMER DRAWING	DRAWING NO 494094-E		
		SCALE 2:1	RESTRICTED TO -		
		SHEET 1 OF 1	REV A2		