



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL RELEASE	08JUL2020	SB	LI



SCHEMATIC

TYPICAL INSERTION LOSS
COMMON MODE 50/50Ω; DIFFERENTIAL MODE 50/50Ω

MHz	0.01	0.05	0.15	0.5	1	3	5	10	30
CM	31	33	44	61	56	47	43	36	21
DM	44	45	43	56	47	33	27	22	22



LABEL TO TE
MARKING SPECIFICATION

SAFETY ORGANIZATIONS

THIS FILTER WILL BE FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS WILL BE MET:

UL RECOGNIZED* 150A 520V 50Hz/60Hz 50°C
CSA CERTIFIED** 150A 520V 50Hz/60Hz 50°C
*31 JULY 2020 ; **31 AUGUST 2020

OPERATING SPECIFICATION

LINE CURRENT/VOLTAGE: 150A, 520VAC
LINE FREQUENCY: 50/60Hz

MAXIMUM LEAKAGE CURRENT: 11mA @ 230VAC, 50Hz

OPERATING AMBIENT TEMPERATURE RANGE @ RATED CURRENT: -10°C TO +50°C

IN AN AMBIENT, T_a, HIGHER THAN 50°C, THE MAXIMUM OPERATING CURRENT, I_o, IS AS FOLLOWS:

$$I_o = I_r \sqrt{\frac{105 - T_a}{55}}$$

RELIABILITY SPECIFICATIONS

STORAGE TEMPERATURE: -40°C TO +85°C
HUMIDITY: 21 DAYS @ 40°C AND 95% RH

TEST SPECIFICATIONS

INDUCTANCE, NOMINAL: 0.2mH

CAPACITANCE @ 1kHz
NEUTRAL TO GROUND, NOMINAL: 2.2μF
LINE TO NEUTRAL, NOMINAL: 13.2μF

DISCHARGE RESISTOR



L/L I.R. 2MΩ 2W
L/N I.R. 1.5MΩ 2W
L/G I.R. 2MΩ 2W
N/G I.R. 680KΩ 2W
IR (NO DISCHARGE RESISTOR) 20°C, 50% RH AND 100VDC, MIN: 6MΩ

RECOMMENDED RECEIVING INSPECITON HIPOI

LINE TO GROUND FOR 1 MINUTE: 2856VDC
LINE TO LINE FOR 1 MINUTE: 2236VDC
LINE TO NEUTRAL FOR 1 MINUTE: 1290VDC

FILTER APPROVAL

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02MAR2020 SHRICARANA B	 TE Connectivity		
		CHK 02MAR2020 LEO IRUDHAYARAJ			
		APVD 02MAR2020 LEO IRUDHAYARAJ			
		PRODUCT SPEC			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME POWER LINE FILTER 150KEVD10BBSW		
		0 PLC ±0.5 1 PLC ±0.40 2 PLC ±0.130 3 PLC ±0.0500 4 PLC ANGLES ±0.5	SIZE A3		
MATERIAL		FINISH	CAGE CODE 00779		
			DRAWING NO 5-1609998-8		
			RESTRICTED TO		
			SCALE 1:4 SHEET 1 OF 2 REV B		
			CUSTOMER DRAWING		






© 2020 TE Connectivity. All Rights Reserved.



NOTE 1 GROUND CONNECTION:
DO NOT LOOSEN INNER GROUND NUTS.
TORQUE OUTER TERMINAL SCREWS: 6 Nm / 54 in.lbs
TORQUE GROUND NUTS: 4-10Nm

NOTE 2 INPUT OUTPUT CONNECTION TERMINAL
AWG SIZE: 6-1 AWG
WIRE SECTION: 50mm²
THREADED BOLT SIZE FOR GROUND: M10

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02MAR2020 SHRICHARANA B	 TE Connectivity		
DIMENSIONS: mm		CHK 02MAR2020 LEO IRUDHAYARAJ			
		APVD 02MAR2020 LEO IRUDHAYARAJ			
		PRODUCT SPEC			
		APPLICATION SPEC	NAME POWER LINE FILTER 150KEVD10BBSW		
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO
-		-	A3	00779	C-5-1609998-8
FINISH		CUSTOMER DRAWING	SCALE	SHEET	REV
-			1:4	2 OF 2	B