


LOC	DIST	REVISIONS					
CE	16	P	LTR	DESCRIPTION		DATE	DWN
			F	REVISED PER ECR-05-17190		12DEC05	JWD
							JD

1

MAXIMUM CONNECTOR INSERTION LOSS IS 2.0dB
PLUS CABLE ATTENUATION OF 3.0dB/km AT 1300nm
(SEE TABLE)



2.04	15.24±0.30 [600.0±11.8]	502150-8
2.02	6.10±0.08 [240.2±3.2]	502150-7
2.14	45.72±0.46 [1800.0±18.0]	502150-6
2.03	10.00±0.15 [393.7±5.9]	502150-5
2.02	6.00±0.08 [236.2±3.2]	502150-4
2.02	5.00±0.08 [196.9±3.2]	502150-3
2.01	3.00±0.05 [118.1±2.0]	502150-2
2.00	1.00±0.05 [39.4±2.0]	502150-1
MAX IL (dB)	L METERS [INCHES]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.URICH	03JUL96	tyco Electronics		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: METERS [INCHES]		CHK R.PAUL	03JUL96				
	TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	APVD N.MILLER		NAME			
		PRODUCT SPEC		CABLE ASSEMBLY, FIBER OPTIC, 100/140 FSMA (905) TO FSMA (905)			
		APPLICATION SPEC		-			
MATERIAL -	FINISH -	WEIGHT -		SIZE A2	CAGE CODE 00779	DRAWING NO C-502150	RESTRICTED TO -
		CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 1	REV F