

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REVISED PER ECO-12-017504	05OCT2012	KH	JE

- 2

PHOSPHOR BRONZE
- 3

LCP, UL94V-0
- 4

FINISH:
CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF
TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON
TELCORDIA GR-1217-CORE; APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
COMPLIANT PIN AREA: 0.5µm MIN MATTE TIN OVER BASE PLATING.
- 5


CONNECTOR MARKED WITH PART NUMBER AND DATE CODE
- 6

REFERENCE APPLICATION SPEC 114-13020 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 7




APPLICATION SEATING HEIGHT TO PRINTED CIRCUIT BOARD
- 8

DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 9


CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995



SECTION B-B



RECOMMENDED
PRINTED CIRCUIT BOARD
LAYOUT
COMPONENT SIDE OF PRINTED CIRCUIT BOARD



5.50	14.50	9.7	5120680-2
5.50	13.00	8.2	5120680-1
N	M	L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARBO	07DEC04	TE TE Connectivity NAME HEADER ASSEMBLY, 30 POSITION, FEED THROUGH, RIGHT HAND, 6 ROW, Z-PACK HS3	
DIMENSIONS:		CHK R. PATTERSON	07DEC04		
mm		APVD R. PATTERSON	07DEC04		
		PRODUCT SPEC			
		APPLICATION SPEC		SIZE A1	
MATERIAL		WEIGHT		CAGE CODE 00779	
HOUSING: 3				DRAWING NO 5120680	
CONTACTS: 2		SIGNAL CONTACT: 4		RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE 5:1	
				SHEET 1	
				OF 1	
				REV A	