


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F2	REVISED PER ECR-24-228032	16DEC2024	BN	ES

SUGGESTED MATING TAB



1 - MATL: ½H BRASS OR NICKEL PL STEEL.




2 - NO BURRS PERMISSIBLE AT HOLE.

3 - MUST BE FLAT WITHIN 0.076[.003] OVER THIS LENGTH.


4 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225°F.

5 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076[.003]


* TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



- 1 DFE SYMBOL PER TABLE
- 2 PREPRODUCTION - FASR REQUIRED
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



3D VIEW



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 7/3/96	TE Connectivity Ltd.		
DIMENSIONS: mm [INCHES]		CHK M FEHER 7/3/96			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J GILLESPIE 7/3/96	NAME		
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.25 [.010] 4 PLC ± - ANGLES ± -	PRODUCT SPEC APPLICATION SPEC	HOUSING, RECT, POSITIVE-LOCK, MKIII, 2 CIRCUIT, 6.35 [.250] SERIES		
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=521119
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 3	REV F2	RESTRICTED TO -

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

OBSOLETE	>PA<	BROWN	66/6 NYLON,V0	2 1-521119-7
OBSOLETE	>PA<	YELLOW	66/6 NYLON,V0	2 1-521119-6
OBSOLETE	>PA<	GREEN	66/6 NYLON,V0	2 1-521119-5
OBSOLETE	>PA<	BLACK	66/6 NYLON,V0	2 1-521119-4
OBSOLETE	>PA<	RED	66/6 NYLON,V0	2 1-521119-3
OBSOLETE	>PA<	BLUE	66/6 NYLON,V0	2 1-521119-2
	>PA<	NATURAL	66/6 NYLON,V0	1-521119-1
OBSOLETE	>PA<	BROWN	6/6 NYLON,V2	2 1-521119-0
OBSOLETE	>PA<	YELLOW	6/6 NYLON,V2	2 521119-9
OBSOLETE	>PA<	GREEN	6/6 NYLON,V2	2 521119-8
OBSOLETE	>PA<	BLACK	6/6 NYLON,V2	2 521119-7
OBSOLETE	>PA<	RED	6/6 NYLON,V2	2 521119-6
	>PA<	NATURAL	6/6 NYLON V0, GWT	521119-5
OBSOLETE	>PA<	BLUE	6/6 NYLON	6 521119-4
	>PA<	PUTTY		6 521119-2
	>PA<	NATURAL		521119-1
DFE SYMBOL		COLOR	MATERIAL	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN JR RUTH 7/3/96	TE TE Connectivity Ltd.
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK M FEHER 7/3/96	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.25 [.010] 4 PLC ± -		APVD J GILLESPIE 7/3/96	
	ANGLES ± -		PRODUCT SPEC	
MATERIAL		FINISH	APPLICATION SPEC	NAME
SEE TABLE		SEE TABLE	WEIGHT -	SIZE A2
CUSTOMER DRAWING			SCALE 4:1	CAGE CODE 00779
			DRAWING NO C=521119	RESTRICTED TO -
			SHEET 2 of 3	REV F2