







LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REVISED PER ECO-12-017504	08OCT2012	KH	JE
			B	REV PER ECO-13-002419	11FEB2013	BC	RP



- 2 PHOSPHOR BRONZE
- 3 LCP, UL94V-0
- 4 FINISH:
CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF
TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON
TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
COMPLIANT PIN AREA: 0.5µm MIN MATTE TIN OVER BASE PLATING.
- 5 CONNECTOR MARKED WITH PART NUMBER AND DATE CODE
- 6 REFERENCE APPLICATION SPEC 114-13020 FOR
RECOMMENDED PLATED THRU HOLE DIAMETER AND
PLATING THICKNESS.
- 7 APPLICATION SEATING HEIGHT TO PRINTED CIRCUIT BOARD
- 8 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 9 CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995



RECOMMENDED
PRINTED CIRCUIT BOARD
LAYOUT
COMPONENT SIDE OF PRINTED CIRCUIT BOARD



ROWS B,C,D,E,F ROW A2 THRU A8	PIN LOCATIONS A1 & A10	5120855-1
SIGNAL CONTACT TYPE B QTY: 58 9.7 LENGTH REF	SIGNAL CONTACT TYPE A QTY: 2 8.2 LENGTH REF	AMP PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARBO	09DEC04	TE Connectivity		
DIMENSIONS:		CHK R. PATTERSON	09DEC04			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. PATTERSON	09DEC04	NAME		
mm		PRODUCT SPEC				
0 PLC ±		APPLICATION SPEC		SIZE		
1 PLC ±		WEIGHT				
2 PLC ±0.13		CAGE CODE	DRAWING NO	RESTRICTED TO		
3 PLC ±0.05		00779	5120855			
4 PLC ±		CUSTOMER DRAWING		SCALE		
ANGLES FINISH						
MATERIAL				SHEET		
HOUSING: 3						
CONTACTS: 2				OF		
SIGNAL CONTACT: 4						