

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
HDIST
-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECN EH10 0344 05	31marc2005	MG	MG
	A1	REVISED PER ECO-09-026495	28NOV09	KK	AEG
	A2	REVISED AS PER ECN-24-279450	13AUG24	MK	GC

	NUMBER OF POSITIONS	L MAX.	
		M.M.	INCHES
5161800 -3	3	7,5	.296
5161800 -4	4	10,0	.394
5161800 -5	5	12,5	.493
5161800 -6	6	15,0	.591
5161800 -7	7	17,5	.690
5161800 -8	8	20,0	.788
5161800 -9	9	22,5	.886
5161800 -0	10	25,0	.985
5161800 -1	11	27,5	1.083
5161800 -2	12	30,0	1.182
5161800 -3	13	32,5	1.280
5161800 -4	14	35,0	1.378
5161800 -5	15	37,5	1.477
5161800 -6	16	40,0	1.575
5161800 -7	17	42,5	1.674
5161800 -8	18	45,0	1.772
5161800 -9	19	47,5	1.871
2- 5161800 -0	20	50,0	1.969

1
OBSOLETE

1
OBSOLETE
OBSOLETE

1
OBSOLETE

1
OBSOLETE

1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

2	CONTACT	PHOSPHORBRONZE	TIN OVER NICKEL	SEE TABLE
1	HOUSING	PBT, 20% GF	GREEN	1
ITEM NO.	DESCRIPTION	MATERIAL	FINISH	QUANTITY

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
	0 PLC	±	
	1 PLC	±	
	2 PLC	±	
	3 PLC	±	
	4 PLC	±	
ANGLES		±	
MATERIAL		FINISH	

DWN	31 mar 05
CHK	M.Gosselink
APVD	M.Gosselink
PRODUCT SPEC	108-19027
APPLICATION SPEC	-
WEIGHT	-
CUSTOMER DRAWING	

tyco <i>Electronics</i>		TYCO ELECTRONICS NEDERLAND B.V. 's-HERTOGENBOSCH, THE NETHERLANDS		
NAME 3-20 POS FEMALE BOARD TO BOARD CONNECTOR ASSEMBLY FOR MINI-MATCH INTERCONNECTION SYSTEM, PITCH 2.5 MM				
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
A3	00779	C-5161800	-	
SCALE		SHEET	OF	REV
				A1