


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	L	REVISED PER ECR-24-207629	15MAY2024	SA	DSC



M7928/4-103, CLASS 1 M7928/13-103, CLASS 1	1000	LOOSE PIECE	53409-1
MILITARY P/N & CLASS	QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 150°C[302°F] MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.26-1.65mm²[509-3260] STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -
MATERIAL	FINISH

DWN DK SCHRUM 06/16/93	TE Connectivity			
CHK RE HERSEY 7/6/93				
APVD M ELLIS 7/6/93				
PRODUCT SPEC				
APPLICATION SPEC	NAME TERMINAL, RING TONGUE, PVF2 , PIDG WIRE SIZE: 22-16 AWG			
NOT AVAILABLE	SIZE A3	CAGE CODE 00779	DRAWING NO C=53409	RESTRICTED TO —
WEIGHT —	CUSTOMER DRAWING			
SCALE 4:1		SHEET 1 OF 1	REV L	