



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P	REVISED PER ECR-24-207629	15MAY2024	SA	DSC



- 1 STAMP AMP 16-14* APPROX AS SHOWN.
- 2 WIRE INSULATION : $\phi 2.667-3.810[\phi .105-.150]$
- 3 BODY MATERIAL THK: $0.787 \pm 0.051[.031 \pm .002]$
- 4 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 5 MEETS M7928/4-107, CLASS 1
MEETS M7928/13-107, CLASS 1
- 6 NOTE DELETED
- 7 MATERIAL:
BODY & SLEEVE: COPPER PER ASTM B152
INSULATION: PVF2
- 8 FINISH:
BODY & SLEEVE: TIN/LEAD (93-7) PLATE PER
ASTM B545 (3% MIN LEAD CONTENT)
INSULATION: COLOR-NATURAL.

1000	LOOSE PIECE	5 53416-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 150°C [302°F] MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN JR RUTH 25OCT07		 TE Connectivity									
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS			VOLTAGE RATING: N/A		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK T MICHIELUTTI 25OCT07											
							APVD T MICHIELUTTI 25OCT07		NAME TERMINAL, RING TONGUE, PVF2 , P.I.D.G. WIRE SIZE: 16-14 AWG											
							PRODUCT SPEC —													
							APPLICATION SPEC 114-2157													
FOR APPLICATION TOOLING INFORMATION			TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] STRANDED		MATERIAL 		FINISH 		WEIGHT —		SIZE A3		CAGE CODE 00779		DRAWING NO C-53416		RESTRICTED TO —	
FOR ORDER ENTRY			1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		CUSTOMER DRAWING						SCALE 4:1		SHEET 1 OF 1		REV P			