

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	S	REVISED PER ECR-24-207629	15MAY2024	SA	DSC

- 1

STAMP AMP 16-14* APPROX AS SHOWN
- 2


WIRE INSULATION DIA: 2.67-3.81[.105-.150]
- 3

TONGUE MATERIAL THK: 0.79±0.05[.031±.002]
- 4

APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 5

MEETS M7928/4-154, CLASS 1
MEETS M7928/13-154, CLASS 1
- 6

NOTE DELETED



100	LOOSE PIECE, BOX	SAME AS 53419-1	8-53419-1
1000	LOOSE PIECE	BODY: COPPER PER ASTM B152 TIN/LEAD (93-7) PLATE PER ASTM B545 (3% MIN LEAD CONTENT) SLEEVE: COPPER PER ASTM B152 TIN/LEAD (93-7) PLATE PER ASTM B545 (3% MIN LEAD CONTENT) INSULATION: PVF2, COLOR-NATURAL	5 53419-1
QTY	PACKAGE TYPE	MATERIAL & FINISH	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 150°C [302°F] MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 25OCT07		 TE Connectivity														
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.20[.008] 4 PLC ± - ANGLES ± -		CHK T MICHELUTTI 25OCT07		APVD T MICHELUTTI 25OCT07				NAME TERMINAL, RING TONGUE, P.VF2 , P.I.D.G. WIRE SIZE: 16-14 AWG							
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] STRANDED						PRODUCT SPEC -		APPLICATION SPEC -		WEIGHT -		SIZE A3		CAGE CODE 00779		DRAWING NO C=53419		RESTRICTED TO -	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		SEE TABLE		SEE TABLE		CUSTOMER DRAWING				SCALE 4:1		SHEET 1 OF 1		REV S					