

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
G1		PER ECR-24-226002	21NOV2024	GC	JM

- NOTES:
- 1

MATERIAL CONTACTS; PHOSPHORBRONZE
MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
- 2

GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1,27µm NICKEL MIN.
AND ACTION PIN: 0,5µm TIN MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
- 3

CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.
- 4

CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 1.
- 5

CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA
GR-1217-CORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
- 6

CONNECTOR LUBRICATED WITH TELCORDIA APPROVED LUBRICANT.
- 8

ASSEMBLY PRINTED WITH P/N AND DATECODE
THE MARKING CAN APPEAR ON THE FRONT SIDE OR BACK SIDE.
- 9





HOLE PATTERN FOR FEMALE CONNECTOR TYPE B
125 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
- 10

ROW "r" 13 PLATED THROUGH HOLES FOR UPPERSHIELD
- 11


SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED
ADHESIVE TAPE OR ADHESIVE
- 12

BASIC P.N. LOWERSHIELD: 5338110
- 13

0.76µm MIN GOLD PLATING AT MATING SURFACE.



COMPONENT SIDE AS SHOWN
RECOMMENDED PCB-HOLE LAY-OUT
SCALE 2,5:1



P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION

OBSOLETE	2 3 7 13	1	3-5352069-0
	2 3 6 7	1	5352069-9
	2 4 7	1	5352069-4
	2 3 7	1	5352069-1
FINISH		MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
±0.2

MATERIAL
-

DWN
K.N.KIRAN
17AUG2004

CHK
B.MOOLJ
24SEP2004

APVD
B.MOOLJ
24SEP2004

PRODUCT SPEC
108-19082

APPLICATION SPEC
114-19029

WEIGHT
0.000000

CUSTOMER DRAWING

NAME
TE Connectivity

Z-PACK 2mm HM
TYPE B - 25 COLUMNS
PRE-SHIELDED RECEPTACLE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=5352069

RESTRICTED TO
-

SCALE
5:1

SHEET
1 of 1

REV
G1