




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R	RESIN SUPPLIER CHANGE FOR THE HOUSING	03DEC2021	SCB	KJK

12	11	96.52[3.800]	99.06[3.900]	78		9-535598-0
12	11	93.98[3.700]	96.52[3.800]	76		8-535598-9
12	11	91.44[3.600]	93.98[3.700]	74		8-535598-8
12	11	88.90[3.500]	91.44[3.600]	72		8-535598-7
12	11	86.36[3.400]	88.90[3.500]	70		8-535598-6
12	11	83.82[3.300]	86.36[3.400]	68		8-535598-5
12	11	81.28[3.200]	83.82[3.300]	66		8-535598-4
12	11	78.74[3.100]	81.28[3.200]	64		8-535598-3
12	11	76.20[3.000]	78.74[3.100]	62		8-535598-2
12	11	71.12[2.800]	73.66[2.900]	58		8-535598-1
12	11	68.58[2.700]	71.12[2.800]	56		8-535598-0
12	11	66.04[2.600]	68.58[2.700]	54		7-535598-9
12	11	63.50[2.500]	66.04[2.600]	52		7-535598-8
12	11	58.42[2.300]	60.96[2.400]	48		7-535598-7
12	11	55.88[2.200]	58.42[2.300]	46		7-535598-6
12	11	53.34[2.100]	55.88[2.200]	44		7-535598-5
12	11	50.80[2.000]	53.34[2.100]	42		7-535598-4
12	11	99.06[3.900]	101.60[4.000]	80		7-535598-3
12	11	73.66[2.900]	76.20[3.000]	60		7-535598-2
12	11	60.96[2.400]	63.50[2.500]	50		7-535598-1
12	11	48.26[1.900]	50.80[2.000]	40		7-535598-0
12	11	45.72[1.800]	48.26[1.900]	38		6-535598-9
12	11	43.18[1.700]	45.72[1.800]	36		6-535598-8
12	11	40.64[1.600]	43.18[1.700]	34		6-535598-7
12	11	38.10[1.500]	40.64[1.600]	32		6-535598-6
12	11	35.56[1.400]	38.10[1.500]	30		6-535598-5
12	11	33.02[1.300]	35.56[1.400]	28		6-535598-4
12	11	30.48[1.200]	33.02[1.300]	26		6-535598-3
12	11	27.94[1.100]	30.48[1.200]	24		6-535598-2
12	11	25.40[1.000]	27.94[1.100]	22		6-535598-1
12	11	22.86[.900]	25.40[1.000]	20		6-535598-0
12	11	20.32[.800]	22.86[.900]	18		5-535598-9
12	11	17.78[.700]	20.32[.800]	16		5-535598-8
12	11	12.70[.500]	15.24[.600]	12		5-535598-7
11	10	10.16[.400]	12.70[.500]	10		5-535598-6
11	10	7.62[.300]	10.16[.400]	8		5-535598-5
11	10	5.08[.200]	7.62[.300]	6		5-535598-4
11	10	2.54[.100]	5.08[.200]	4		5-535598-3
OBSOLETE			2.54[.100]	2	$\triangle_6$	5-535598-2
12	11	15.24[.600]	17.78[.700]	14		5-535598-1
12	11	96.52[3.800]	99.06[3.900]	78		4-535598-0
12	11	93.98[3.700]	96.52[3.800]	76		3-535598-9
12	11	91.44[3.600]	93.98[3.700]	74		3-535598-8
12	11	88.90[3.500]	91.44[3.600]	72		3-535598-7
12	11	86.36[3.400]	88.90[3.500]	70		3-535598-6
12	11	83.82[3.300]	86.36[3.400]	68		3-535598-5
12	11	81.28[3.200]	83.82[3.300]	66		3-535598-4
12	11	78.74[3.100]	81.28[3.200]	64		3-535598-3
12	11	76.20[3.000]	78.74[3.100]	62		3-535598-2
12	11	71.12[2.800]	73.66[2.900]	58		3-535598-1
12	11	68.58[2.700]	71.12[2.800]	56		3-535598-0
12	11	66.04[2.600]	68.58[2.700]	54		2-535598-9
12	11	63.50[2.500]	66.04[2.600]	52		2-535598-8
12	11	58.42[2.300]	60.96[2.400]	48		2-535598-7
12	11	55.88[2.200]	58.42[2.300]	46		2-535598-6
12	11	53.34[2.100]	55.88[2.200]	44		2-535598-5
12	11	50.80[2.000]	53.34[2.100]	42		2-535598-4
35598-3	12	99.06[3.900]	101.60[4.000]	80		2-535598-3
12	11	73.66[2.900]	76.20[3.000]	60		2-535598-2
12	11	60.96[2.400]	63.50[2.500]	50		2-535598-1
12	11	48.26[1.900]	50.80[2.000]	40		2-535598-0
12	11	45.72[1.800]	48.26[1.900]	38		1-535598-9
12	11	43.18[1.700]	45.72[1.800]	36		1-535598-8
12	11	40.64[1.600]	43.18[1.700]	34		1-535598-7
12	11	38.10[1.500]	40.64[1.600]	32		1-535598-6
12	11	35.56[1.400]	38.10[1.500]	30		1-535598-5
12	11	33.02[1.300]	35.56[1.400]	28		1-535598-4
12	11	30.48[1.200]	33.02[1.300]	26		1-535598-3
12	11	27.94[1.100]	30.48[1.200]	24		1-535598-2
12	11	25.40[1.000]	27.94[1.100]	22		1-535598-1
12	11	22.86[.900]	25.40[1.000]	20		1-535598-0
12	11	20.32[.800]	22.86[.900]	18		535598-9
12	11	17.78[.700]	20.32[.800]	16		535598-8
12	11	12.70[.500]	15.24[.600]	12		535598-7
12	10	10.16[.400]	12.70[.500]	10		535598-6
12	10	7.62[.300]	10.16[.400]	8		535598-5
12	10	5.08[.200]	7.62[.300]	6		535598-4
12	10	2.54[.100]	5.08[.200]	4		535598-3
12	10	-	2.54[.100]	2	$\triangle_6$	535598-2
12	10	15.24[.600]	17.78[.700]	14		535598-1



- | | |
|----|---|
| 1 | HOUSING: FLAME RETARDANT, GLASS FILLED, POLYESTER, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE |
| 2 | CONTACT: DUPLEX PLATED 0.25μm[.000010] MIN GOLD IN CONTACT AREA, 3.81–7.62μm[.000150–.000300] BRIGHT TIN–LEAD ON LEADS, ALL OVER 1.27μm[.000050] NICKEL |
| 3 | THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY – NOT TO CONTACT LOCATIONS |
| 4 | MARK PART NUMBER AND DATE CODE IN APPROXIMATE LOCATION SHOWN, EITHER SIDE. |
| 5 | TOLERANCE IS NON–CUMULATIVE. |
| 6 | 2 POSITION DATE CODE IS MARKED OPPOSITE SIDE OF TE CONNECTIVITY LOGO. |
| 7 | POINT–OF–MEASUREMENT DIMENSION FOR PLATING THICKNESS (INSIDE CONTACT BEAM). |
| 8 | POINT–OF–CONTACT DIMENSION. |
| 9 | TE CONNECTIVITY TRADEMARK AND CSA LOGO ARE MOLDED INTO HOUSING, THIS LOCATION. |
| 10 | NO PART NUMBER MARKING REQUIRED FOR THIS PART. |
| 11 | CONTACT: DUPLEX PLATED 0.25μm[.000010] MIN GOLD IN CONTACT AREA, 3.81–7.62μm[.000150–.000300] MATTE TIN ON LEADS, ALL OVER 1.27μm[.000050] MIN NICKEL |
| 12 | ROHS 2002/95/EC COMPLIANT. |

THIS DRAWING IS A CONTROLLED DOCUMENT		DWG. NO. 06N0V2002		 TE Connectivity	
		CHKD. 06N0V02			
DIMENSIONS: mm		TOLERANCES: UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, 100X.100CL, VERTICAL MOUNT, AMPMODU	
		0 P/LC ± 0.1 2 P/LC ± 0.1 2 P/LC ± 0.1 [0.05] 2 P/LC ± 0.1 4 ANGLES ± 0.1 FINISH			
MATERIAL		PRODUCT SPEC		SIZE CASE CODE DRAWING NO	
		108-25022 APPLICATION SPEC 114-25018 WEIGHT —		A1 00779 C=535598	
CUSTOMER DRAWING				SCALE 1:1 SHEET 1 of 1 REV R	