



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER ECR-24-207629	16MAY2024	SA	DSC

- 1

STAMP "AMP 16-14 HD*" LOCATED APPROX AS SHOWN.
- 2 TONGUE MATERIAL THK IS .050 MAX
- 3 FOR .230 MAX WIRE INSULATION DIA.



BODY & SLEEVE: COPPER PER ASTM B152 TIN LEAD (93-7) PLATE PER ASTM B545 (3% MIN LEAD CONTENT)	53984-1
INSULATION: PVF2, COLOR - NATURAL	
MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 14SEP04	TE Connectivity									
		CHK T MICHELUTTI 14SEP04										
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T MICHELUTTI 14SEP04	NAME WIRE TERMINAL PVF2 – PIDG – RING TONGUE WIRE SIZE : 16–14 HD									
	0 PLC ± – 1 PLC ± – 2 PLC ± – 3 PLC ± .008 4 PLC ± – ANGLES ± 5°	PRODUCT SPEC –										
MATERIAL –	FINISH –	APPLICATION SPEC –	SIZE		CAGE CODE	DRAWING NO		RESTRICTED TO				
		WEIGHT –	A3		00779	C-53984		–				
CUSTOMER DRAWING			SCALE		5:1		SHEET		1 OF 1		REV	D