
TITLE

TWO CONDUCTOR CABLE, SHIELDED, JACKETED, OUTER SPACE, 600 VOLT

Date 6-12-07

vision R

This specification sheet forms a part of the latest issue of Raychem Specification 55/.



- RADIATION-CROSSLINKED, MODIFIED ETFE

CABLE CONSTRUCTION DETAILS							
PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)		MAXIMUM WEIGHT
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	(lbs/1000 ft.)
55/1121-26-*	26	38	.006	.008	.097	.102	7.9
55/1121-24-*	24	38	.006	.008	.107	.112	9.8
55/1121-22-*	22	38	.006	.008	.119	.125	12.2
55/1121-20-*	20	38	.006	.008	.133	.140	16.2
55/1121-18-*	18	38	.006	.008	.153	.161	21.9
55/1121-16-*	16	38	.006	.008	.169	.177	26.6
55/1121-14-*	14	38	.006	.008	.203	.213	38.4
55/1121-12-*	12	38	.007	.009	.241	.253	55.1

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C Maximum continuous conductor temperature VOLTAGE RATING: 600 volts (rms) at sea level CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

JACKET COLOR: White preferred JACKET ELONGATION: 50% (minimum)

JACKET FLAWS:

Spark Test, 1000 volts (rms) Impulse Dielectric Test, 6.0 kV (peak)

NOTE: Nominal values are for information only. Nominal values are not requirements.

RADIATION RESISTANCE: 500 megarads SHIELD COVERAGE: 85% (minimum) VACUUM STABILITY:

Total Mass Loss (TML), 1.00% (maximum)
Volatile Condensable Material, 0.10% (maximum)
VOLTAGE WITHSTAND TEST (Post Environmental):
1500 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

1/ Example: AWG 20, black and brown component wires; white jacket: 55/1121-20-0/1-9

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.

Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

RAYCHEM is a trademark of Tyco Electronics Corporation.

Page 1 of 1

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-227-8816 Fax: 1-650-361-6297