


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REVISED PER ECR-24-207629	15MAY2024	SA	DSC

AMP WIRE RANGE
16-14 AWG STRANDED

- 1 WIRE INSULATION DIA 2.67 [.105] TO 3.81 [.150].
- 2 FINISH: BODY AND SLEEVE: TIN/LEAD (93-7) PLATE PER ASTM B545. (3% MIN LEAD CONTENT)
- 3 MATERIAL: BODY AND SLEEVE, COPPER PER ASTM B152 INSULATION: PVF² COLOR- NATURAL



-	50	LOOSE PIECE, BOX	8-53549-2
M7928/6-4 CLASS 1	1000	LOOSE PIECE	53549-1
MILITARY PART NUMBER & CLASS PER MIL-T-7928	QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 150°C	THIS DRAWING IS A CONTROLLED DOCUMENT.		 TE Connectivity						
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: -	DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD 9-28-93 M ELLIS		NAME		SPLICE, BUTT, PVF ² , P.I.D.G., WIRE SIZE: 16-14 AWG		
	FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111			CIRCULAR MIL AREA: 1.04-2.62mm ² [2,050-5,180] STRANDED		PRODUCT SPEC 108-11023				APPLICATION SPEC -
FOR ORDER ENTRY 1-800-526-5142			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL 	FINISH 	WEIGHT -		SIZE A3	CAGE CODE 00779	DRAWING NO C-53549	RESTRICTED TO -
CUSTOMER DRAWING							SCALE 1:1		SHEET 1 OF 1		REV N	