SPECIFICATION CONTRO	L DRAWING	SCD	55/LF0314
Title WIRE, RADIATION-CROSSLINKED, MODIFIED ET ULTRA LOW FLUORIDE, ULTRA LIGHTWEIGHT, OUT	,	Date 6-7-17	Revision C
This specification sheet forms a par	t of the latest issue of Raychem S	Specification 55/.	
CONDUCTOR - SILVER-COATED HIGH-STRENGTH COPPER ALLOY	INSI	JLATION - ULTRA LOW RADIATION- MODIFIED E	CROSSLINKED,

	TABLE I. CONSTRUCTION DETAILS						
	SIZE	CONDUCTOR STRANDING (number x AWG)	DIAMETER OF STRANDED CONDUCTOR (inch)		FINISHED WIRE		
PART NUMBER <u>1</u> /					MAXIMUM RESISTANCE AT 20°C	DIAMETER (inch)	MAXIMUM WEIGHT
			MINIMUM	MAXIMUM	(ohms/1000 ft.)	((lbs/1000 ft.)
55/LF0314-30-*	30	7 x 38	.0110	.0120	117.4	.0195 ± .0015	.52
55/LF0314-28-*	28	7 x 36	.0140	.0150	74.4	.0225 ± .0015	.76
55/LF0314-26-*	26	19 x 38	.0175 .0191	44.8	.0274 ± .0017	1.22	
55/LF0314-24-*	24	19 x 36	.0225	.0241	28.4	.0322 ± .0017	1.79
55/LF0314-22-*	22	19 x 34	.0285	.0301	17.5	.0390 ± .0017	2.70
55/LF0314-20-*	20	19 x 32	.0365	.0385	10.7	.0495 ± .0017	4.27

	TABLE II. PERFORMANCE DETAILS			
	CROSSLINKED VERIFICATION - BEND TESTING			
PART NUMBER <u>1</u> /	MANDREL DIAMETER (inch) (± 3%)	WEIGHT (lb) (± 3%)		
55/LF0314-30-*	.250	.063		
55/LF0314-28-*	.250	.063		
55/LF0314-26-*	.375	.063		
55/LF0314-24-*	.375	.125		
55/LF0314-22-*	.500	.188		
55/LF0314-20-*	.500	.250		

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. TE Connectivity also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.					
	1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.				
		Raychem, TE Connectivity, and TE Connectivity (logo) are trademarks.		Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800	
	Dana 4 at 0	DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL.	- TF		
Page 1 of 2	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.	connectivity	Phone: 1-800-522-6752 Fax: 1-650-361-6297		

© 2007-2017 TE Connectivity Ltd. family of companies. All Rights Reserved.



SCD

WIRE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature VOLTAGE RATING: 600 volts (rms) at sea level COLOR: White preferred CONCENTRICITY: 80% (minimum) CROSSLINKED VERIFICATION: 300 ± 3°C for 1 hour FLUORIDE EXTRACTION: 70 ± 2°C for 168 hours, 20 ppm (maximum) IDENTIFICATION AND COLOR STRIPING DURABILITY: 125 cycles (250 strokes) (minimum), 500 g weight INSULATION ELONGATION: 50% (minimum) **INSULATION FLAWS:** Spark Test, 1.5 kV (rms) (30-24 AWG) 3.0 kV (rms) (22-20 AWG) Impulse Dielectric Test, 6.0 kV (peak) INSULATION THICKNESS: .004 in. (nominal) **RADIATION RESISTANCE: 500 megarads** SHRINKAGE: 230 ± 3°C for 1 hour, 0.125 in. (maximum) in 12 inches VACUUM STABILITY: Total Mass Loss (TML), 1.00% (maximum) Volatile Condensable Material (VCM): 0.10% (maximum) VOLTAGE WITHSTAND (Post Environmental): 1500 volts (rms), 60 Hz, 5 minutes

1/ PART NUMBER:

The "*" in the part numbers in Tables I and II shall be replaced by a color code designator. Example: AWG 22, white: 55/LF0314-22-9 AWG 22, white with a black stripe: 55/LF0314-22-90