


LOC		DIST		REVISIONS						
AA		26		P	LTR	DESCRIPTION		DATE	OWN	APVD
					AJ	REV; EC 067A-0237-98		11 JAN99	DLG	DLK



- THIS KIT SHIPPED NOT ASSEMBLED.
- MATERIAL:
COLLAR, BODY AND COVERS-POLYESTER, BLACK.
STRAIN RELIEFS, HOLE PLUG AND DUST COVER-POLYESTER ELASTOMER, BLACK.
STUFFER BOX-POLYCARBONATE, CLEAR.
SHORTING BAR AND TERMINALS-GOLD PLATED COPPER ALLOY.
GROUND PLANES & FERRULE-TIN PLATED COPPER ALLOY.
LATCH LOCK-PPO, GRAY.
- ELECTRICAL PARAMETERS-1 AMPERE MAX AT 30 VOLTS AC, FOR 22 THROUGH 26 AWG SOLID AND STRANDED WIRE.
- CONNECTOR ASSEMBLY DESIGNED TO FIT SUGGESTED PANEL CUTOUT. PANEL MATERIAL THICKNESS SHALL BE .054-.064 [1.37-1.63].
- REFERENCE TO TYPE REFERS TO ETL CABLE IDENTIFICATIONS.
- THIS CONNECTOR KIT WILL MATE WITH ANY 4 POSITION IEEE LAN DATA CONNECTOR.
- SHORTING MECHANISM IS OPENED UPON MATING CONNECTOR.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS.
- PACKAGED 1 KIT PER POLYBAG, 25 BAGS PER BOX.
- FOR ADDITIONAL INFORMATION SEE INSTRUCTION SHEET IS 3110.
- THESE COMPONENTS CAN BE ORDERED SEPARATELY.
- PACKAGED 1 KIT PER BLISTER PACK.

SUPERSEDED BY	554000-1	12	6-554000-3
		9	554000-1
		PACKAGED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.H. SMITH/UTA 04-FEB-93	03-NOV-92	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: [INCHES [mm]]		CHK N. JONES 04-FEB-93	04-FEB-93	NAME DATA CONNECTOR KIT, 4 POSITION, IEEE 802.5	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PROD SPEC 108-6054		SIZE 108-6054	
0 PLC ±.005		APPL SPEC 114-6033		RESTRICTED TO	
1 PLC ±.005		WEIGHT		A1 00779	
2 PLC ±.005		CUSTOMER DRAWING		SCALE 2:1	
3 PLC ±.005				SHEET 1 OF 1	
4 PLC ±.005				REV AJ	
ANGLES					
FINISH					