





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A2		REVISED AS PER ECR-23-169440	19APR2023	JK	WH


- ⚠ MATERIAL:
HOUSING – PCT POLYESTER, BLACK, UL94V-0.
OVERMOLDED TERMINAL ARRAY – PBT, BROWN.
TERMINALS – 0.33 [.013] THICK PHOS BRONZE
PLATED WITH 1.27µm [.000050] MIN THICK
HARD GOLD IN LOCALIZED AREA AND 3.81µm
[.000150] MIN THICK MATTE TIN IN SOLDER
AREA OVER 1.27µm [.000050] MIN THICK
NICKEL UNDERPLATE.
OUTER SHIELD AND INNER SHIELD – 0.25 [.010]
THICK COPPER ALLOY PLATED WITH 1.27 µm
[.000050] MINMUM NICKELAND 2.03 µm [.000080]
MINIMUM HOT TIN DIPON PCB GROUND TABS.
- ⚠ JACK CAVITY CONFORMS TO FCC RULES AND
REGULATIONS, PART 68 SUBPART F.
- ⚠ DATE CODE LOCATED ON REAR OF PART
APPROXIMATELY AS SHOWN:
FIRST 2 DIGITS ARE LAST 2 DIGITS OF YEAR,
SECOND 2 DIGITS ARE MANUFACTURING
WORK WEEK,
LAST DIGIT IS DAY OF WEEK, WITH SUNDAY = 1.



PC BOARD LAYOUT VIEWED FROM COMPONENT SIDE
SCALE 2:1



SUGGESTED PANEL CUTOUT DIMENSIONS
SCALE 2:1



BACK VIEW

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. FERNANDEZ-DOCKS 15JUN2005	 TE Connectivity				
DIMENSIONS: mm [INCHES]		CHK J. WESTMAN 15JUN2005	NAME				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. FLICKINGER 15JUN2005				
	0. PLC ± -		PRODUCT SPEC				
	1. PLC ± -		108-1163-2				
	2. PLC ± 0.25[.01]		APPLICATION SPEC				
	3. PLC ± 0.13[.005]		114-2048				
4. PLC ± -		ANGLES		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
FINISH		114-2048		A1	00779	5569261	-
MATERIAL		WEIGHT		CUSTOMER DRAWING			
		0.000000		SCALE 4:1			
		A2		SHEET 1 OF 1			
				REV A2			