

D

C

B




A

D


C

B

A



PC BOARD LAYOUT VIEWED FROM COMPONENT SIDE
SCALE 2:1



SUGGESTED PANEL CUTOUT DIMENSIONS
SCALE 2:1

- 1 MATERIAL:
HOUSING - PCT POLYESTER, BLACK, UL94V-0.
OVERMOLDED TERMINAL ARRAY - PBT, BROWN.
TERMINALS - 0.33 [.013] THICK PHOS BRONZE
PLATED WITH 1.27 μ m [.000050] MIN THICK
HARD GOLD IN LOCALIZED AREA AND 3.81 μ m
[.000150] MIN THICK MATTE TIN IN SOLDER
AREA OVER 1.27 μ m [.000050] MIN THICK
NICKEL UNDERPLATE.
OUTER SHIELD AND INNER SHIELD - 0.25 [.010]
THICK COPPER ALLOY PLATED WITH 2.03 μ m
[.000080] MIN BRIGHT TIN OVER 1.27 μ m
[.000050] MIN NICKEL.
- 2 JACK CAVITY CONFORMS TO FCC RULES AND
REGULATIONS, PART 68 SUBPART F.
- 3 DATE CODE LOCATED ON REAR OF PART
APPROX AS SHOWN:
FIRST 2 DIGITS ARE LAST 2 DIGITS OF YEAR,
SECOND 2 DIGITS ARE MANUFACTURING WORK WEEK,
LAST DIGIT IS DAY OF WEEK, WITH SUNDAY = 1.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. FERNANDEZ-DOCKS 13JUN2005	5569250-1 PART NUMBER	
DIMENSIONS: mm [INCHES]		CHK J. WESTMAN 13JUN2005	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. FLICKINGER 13JUN2005	NAME STACKED MODULAR JACK ASSEMBLY, 2 X 2 PORT, 8 POSITION, SHIELDED, CATEGORY 5	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.25[.01] 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-1163-2	SIZE 114-2048	
MATERIAL △		FINISH △	WEIGHT 0.000000	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV A3