SPECIFICATION CONTROL DRAWING

55A6253


TITI F

TWO CONDUCTOR CABLE, SHIELDED, JACKETED

ate 10-16-03 evision

Е

This specification sheet forms a part of the latest issue of Raychem Specification 55A.



CABLE CONSTRUCTION DETAILS							
PARTNUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKETTHICKNESS (inches)		OUTSIDE DIAMETER (inches)		MAXIMUM WEIGHT
			MINIMUM	MAXIMUM	NOMINAL	MAXIMUM	(lb/1000 ft.)
55A6253-26-*	26	38	.005	.010	.113	.119	9.2
55A6253-24-*	24	38	.005	.010	.123	.129	11.0
55A6253-22-*	22	38	.005	.010	.135	.141	14.3
55A6253-20-*	20	38	.005	.010	.151	.158	18.5
55A6253-18-*	18	38	.006	.011	.173	.182	24.6
55A6253-16-*	16	38	.006	.011	.187	.196	29.2
55A6253-14-*	14	38	.007	.012	.223	.234	41.8
55A6253-12-*	12	38	.007	.012	.257	.270	57.8
55A6253-10-*	10	38	.007	.013	.303	.318	85.1
55A6253-8-*	8	36	.009	.017	.433	.455	161.

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature VOLTAGE RATING: 600 volts (rms) at sea level

BLOCKING: 200 ± 3°C for 6 hours

CROSSLINKED VERIFICATION: 300 ± 5°C for 6 hours DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz FLAMMABILITY: Procedure 1, 3 seconds (maximum); 3 in. (maximum); no flaming of facial tissue

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

JACKET FLAWS:

Spark Test, 1500 volts (rms)

Impulse Dielectric Test, 6.0 kV (peak)

NOTE: Nominal values are for information only.

Nominal values are not requirements.

LOW TEMPERATURE-COLD BEND: -55 ± 5 °C for 4 hours

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST (Post Environmental):

1000 volts (rms), 60 Hz, 1 minute

PARTNUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

1/ Example: AWG 20, red and orange component wires; white jacket: 55A6253-20-2/3-9

This cable shall meet all constructional requirements of M27500 (AWGSP2T23)

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.

Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "AXXX".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

DIMENSIONS ARE IN INCHES, AND LINEESS OTHERWISE DESIGNATED ARE NOMINAL

Page 1 of 1

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-227-8816 Fax: 1-650-361-6297