## SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECOGNIZED: UL 1283 CSA CERTIFIED: CSA C22.2 No. 8 VDE APPROVED: EN 60939-2

### OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 55 AMP 277 VAC LINE TO GROUND

AND 480VAC PHASE TO PHASE

50

LINE FREQUENCY: 50-60Hz

MAXIMUM LEAKAGE CURRENT.

@ 277VAC 50 HZ EACH LINE TO GROUND: 8.7 mA

OPERATING AMBIENT TEMP. RANGE: -10°C TO +50°C @ RATED CURRENT, In. IN AN AMBIENT,  $T_0$ , HIGHER THAN 50°C, THE MAXIMUM OPERATING CURRENT,  $I_0$ , IS AS FOLLOWS:  $I_1 = I_1 - I_2 - I_3 = I_4 - I_3 = I_4 - I_4 = I_4 - I_5 = I$  $I_0 = I_r$ <u> 100 - Ta</u>

## RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS @ 50°C 95% RH.
CURRENT OVERLOAD TEST: 6 TIMES Ir FOR 8 SECONDS

#### CUSTOMER DRAWING CATALOG # 55BCF10R APPRVD DATE ECN# 15-015324 200CT15 HS

# TEST SPECIFICATIONS:

INDUCTANCE: 1.80 mH NOMINAL CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C)

LINE TO GROUND: 0.1 μF±20% LINE TO LINE: 6.65 μF±20%


DISCHARGE RESISTOR: 1.5 / .66 M L/G AND L/L I.R. NO DISCHARGE RESISTOR: 6000M₁ (MIN.) 100VDC, 20°C AND 50% RH@

# RECOMMENDED RECEIVING INSPECTION HIPOT:

LINE TO GROUND: 1850 VDC FOR 1 MINUTE LINE TO LINE: 1850 VDC FOR 1 MINUTE

## FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



50 へ - 50 へ(TYPICAL)INSERTION LOSS												
FREQUENCY MHz	.01	.03	.05	.10	.15	.30	.50	1.0	3.0	5.0	10	30
COMMON dB	2	12	20	32	41	55	54	58	55	42	29	14
DIFF. dB	27	35	35	51	68	87	83	71	61	58	54	31
SHEET SIZE	THIRD A	NGLE PRO	5)	THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCUSSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL, VITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION.								

UNLESS OTHERWISE SPECIFIED
TOLERANCE TO BE ±0.64 (±0.025)
MATERIAL & FINISH: AS SUPPLIED
DIMENSIONS IN MM (INCHES) NOTES:

55BCF10R-A.ckd

TE Connectivity

A

CUSTOMER DRAWING

TE PART ND.: 2-1609989-4 NTS 300CT15

DRAWTNG NUMBER 55BCF10R