SPECIFICATION CONTROL DRAWING

55A6053

В


TITLE

FOUR CONDUCTOR CABLE, SHIELDED, JACKETED

9-11-00

Revision

This specification sheet forms a part of the latest issue of Raychem Specification 55A.



		CA	BLE CONSTR	RUCTION DETA	ILS		
PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inch)		OUTSIDE DIAMETER (inch)'		MAXIMUM WEIGHT (lb/1000 ft)
			MINIMUM	MAXIMUM	NOMINAL	MAXIMUM	
55A6053-26-*	26	38	.005	.010	.130	.150	14.7
55A6053-24-*	24	38	.005	.010	.142	.165	18.0
55A6053-22-*	22	38	.005	.010	.154	.179	22.9
55A6053-20-*	20	38	.006	.011	.173	.202	30.4

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) BLOCKING: 200 ± 3°C for 6 hours

CROSSLINK VERIFICATION: 300 ± 5°C for 6 hours DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz FLAMMABILITY: Procedure 1, 3 seconds (maximum);

3 in. (maximum); no flaming of facial tissue

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in2 (minimum)

JACKET FLAWS:

Spark Test, 1.5 kV (rms), 100% test

Impulse Dielectric Test, 6.0 kV (peak), 100% test

LOW TEMPERATURE-COLD BEND: -55 ± 5°C for 4 hours

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST (POST ENVIRONMENTAL):

1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 20, white, white with blue stripe,

white with orange stripe and white with

green stripe component wires;

white jacket: 55A6053-20-9/96/93/95-9

This cable shall meet all constructional requirements of M27500 (AWGSE4S23).

COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

Raychem

300 Constitution Drive, Menlo Park, California 94025 1-800-2 Raychem Fax: 1-650-361-6297

Page 1 of 1