SPECIFICATION CONTROL DRAWING

TITLE

FOUR CONDUCTOR CABLE, FILTER LINE, ELECTROLOSS™, 600 VOLT

Date


6-25-92

Revision

F

55FB1441

This specification sheet forms a part of the latest issue of Raychem Specification 55F.



		(CABLE CONST	RUCTION DETA	ILS		
PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inches)		OUTSIDE DIAMETER (inches)		MAXIMUM WEIGHT
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	(lbs/1000 ft.)
55FB1441-22-*	22	38	.006	.008	.183	.214	32.3
55FB1441-20-*	20	38	.006	.008	.202	.237	41.4
55FB1441-18-*	18	38	.006	.008	.227	.266	54.2
55FB1441-16-* .	16	38	.007	.009	.243	.285	64.0
55FB1441-14-*	14	38	.007	.009	.277	.326	86.5
55FB1441-12-*	12	38	.008	.010	.344	.406	131.
55FB1441-10-*	10	36	.008	.010	.406	.479	193.

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature VOLTAGE RATING: 600 volts (rms) at sea level ACCELERATED AGING (CROSSLINKING PROOF TEST):

300 \pm 3°C for 7 hours

* BLOCKING: 200 ± 3°C for 6 hours

FLAMMABILITY: 3 seconds (maximum); 3 in. (maximum); no flaming of facial tissue

IDENTIFICATION AND COLOR STRIPING DURABILITY: 125 cycles (250 strokes) (minimum), 500 g weight

* IMMERSION: 5% (maximum) diameter increase,

no cracking of jacket

JACKET COLOR: Black

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 3500 lbf/in2 (minimum)

JACKET FLAWS: Not Applicable

* LIFE CYCLE: 200 ± 3°C for 168 hours

LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST (DIELECTRIC): Conductor to conductor and shield, 1500 volts (rms), 60 Hz

VOLTAGE WITHSTAND TEST (POST ENVIRONMENTAL):

Not Applicable

PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators except that violet shall be light violet and the designator shall be 7L; with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 20, light violet component wires; black jacket: 55FB1441-20-7L/7L/7L-0

NOTE: Nominal values are for information only.

Nominal values are not requirements.

* Qualification Test

COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

Raychem

Raychem Corporation 300 Constitution Drive, Menlo Park, California 94025 415) 361 3333 TWX 910 373 1728