SPECIFICATION CONTROL DRAWING

55A6130


TITLE

TWO CONDUCTOR, THERMOCOUPLE EXTENSION CABLE, SHIELDED, JACKETED

6-19-02

Revision

This specification sheet forms a part of the latest issue of Raychem Specification 55A



CABLE CONSTRUCTION DETAILS							
PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inch)		OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lb/1000 ft)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	1 ` '
55A6130-26-*	26	38	.006	.008	.073 x .113	.077 x .119	9.1
55A6130-24-*	24	38	.006	.008	.078 x .123	.082 x .129	10.7
55A6130-22-*	22	38	.006	.008	.083 x .133	.087 x .137	13.1
55A6130-20-*	20	38	.006	.008	.091 x .149	.096 x .153	17.8
55A6130-16-*	16	38	.006	.008	.115 x .197	.121 x .207	34.3

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)

ACCELERATED AGING: 300 ± 3°C for 7 hours DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz FLAMMABILITY: Procedure 1, 3 seconds (maximum);

3 in. (maximum); no flaming of facial tissue JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in2 (minimum)

JACKET FLAWS:

Spark Test, 1000 volts (rms), 100% test

Impulse Dielectric Test, 6.0 kV (peak), 100% test

LIFE CYCLE: 230 ± 3°C for 500 hours

LOW TEMPERATURE-COLD BEND: -65° ± 2°C for 4 hours

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST (POST ENVIRONMENTAL):

1000 volts (rms), 60 Hz, 1 minute

PART NUMBER

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color. The color of CHROMEL® shall be shown first.

Example: AWG 20,

Per MIL-STD-687: white and green; white jacket:

55A6130-20-9/5-9

Per ANSI MC 96.1: yellow and red; yellow jacket:

55A6130-20-4/2-4

Per British Standard Code BS:

brown and blue; red jacket: 55A6130-20-1/6-2

CABLE IDENTIFICATION: Cable shall be marked on outer surface in black ink at 12 in. (nominal) intervals between marks as follows: " 55A6130-AWG 06090 "

EMF shall be 4.00 mV (minimum), 4.19 mV (maximum), at 100°C with reference junction corrected to 0°C per ANSI MC96.1, and shall be performed on every length of finished cable.

The combination of the above thermoelements is referred to as type KX per ANSI MC96.1.

CHROMEL® and ALUMEL® are federally registered trademarks of Hoskins Manufacturing Company. Alternative conductors, exhibiting the same performance characteristics, may be substituted for one or both of the CHROMEL® and ALUMEL® conductors.

COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

Raychem

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

300 Constitution Drive, Menlo Park, California 940 25 1-800-2 Raychem Fax: 1-650-361-6297

Page 1 of 1