






LOC		DIST		REVISIONS				
AD	25	P	LTR	DESCRIPTION		DATE	DWN	APVD
		B		REV PER ECO-12-002590		20FEB2012	WS	RP



- 1 HOUSING MATERIAL: GLASS-FILLED POLYMER.
- 2 POST MATERIAL: COPPER ALLOY.
- 3 POST FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. TIN PLATE ON POSTS.
- 4 ACTION PIN POSTS REQUIRE 2.36[.093] MINIMUM THICK PC BOARD. RECOMMENDED PC BOARD HOLES ARE 1.151[.0453] DIA PLATED THROUGH WITH 0.02-0.08[.001-.003] COPPER AND 0.008[.0003] MINIMUM TIN-LEAD PLATING. FINISHED HOLE AFTER PLATING, 0.94-1.09[.037-.043] DIA.
- 5 [PART NUMBER, DATE CODE] MARKED THIS APPROXIMATE AREA.
- 6 MARKING ON THIS SIDE.



1-50	X	X	X	150	5650924-5
POSITIONS LOADED	C	B	A	NO. OF LOADED POSITION	ASSY PART NUMBER
ROWS LOADED					

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE	ORDECOS	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK A. SHARPE	ORDECOS	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. SHARPE	ORDECOS	PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		SIZE	
1 PLC ± -		WEIGHT		CAGE CODE	
2 PLC ± -		DRAWING NO		RESTRICTED TO	
3 PLC ± 0.13[.005]		A1 00779		5650924	
4 PLC ± -		CUSTOMER DRAWING		SCALE	
ANGLES ± -		5:1		SHEET	
FINISH		1		OF	
		1		REV	
		B			