
<b>SPECIFICATION</b>	CONTROL	DRAWING
----------------------	---------	---------

TWO CONDUCTOR CABLE, DOUBLE SHIELDED, JACKETED, GENERAL PURPOSE, 600 VOLT

55PC6021

С

## This specification sheet forms a part of the latest issue of Raychem Specification 55PC.



CABLE CONSTRUCTION DETAILS										
PART NUMBER <u>1</u> /	CONDUCTOR SIZE (AWG)	OUTER SHIELD	JACKET THICKNESS ( in. )		OUTSIDE DIAMETER ( in. )		WEIGHT ( lbs/1000 ft. )			
		SIZE	SIZE (AWG)	LOWER SPEC LIMIT	TARGET WALL	LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC6021-24-*	24	36	38	.0055	.0070	.129	.133	.137	17.98	18.57
55PC6021-22-*	22	36	38	.0055	.0070	.140	.145	.150	21.71	22.34
55PC6021-20-*	20	36	38	.0055	.0070	.157	.162	.167	25.92	26.59
55PC6021-18-*	18	38	38	.0060	.0075	.173	.177	.182	32.29	33.13
55PC6021-16-*	16	38	38	.0060	.0075	.188	.192	.197	33.98	34.87
55PC6021-14-*	14	38	38	.0060	.0080	.218	.223	.228	49.59	50.72
55PC6021-12-*	12	38	38	.0060	.0080	.256	.261	.267	64.14	65.58
55PC6021-10-*	10	36	36	.0070	.0090	.311	.320	.329	99.52	101.94

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.						
1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902" MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.						
Page 1 of 2	Raychem, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks.		Raychem Wire & Cable			
	DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.		01 Oakside Avenue edwood City, CA 94063-3800			
	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.	connectivity	Phone: 1-800-227-8816 Fax: 1-650-361-6297			

TITLE

© 2013 Tyco Electronics Corporation,. All rights reserved.



Revision

С

SCD

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature VOLTAGE RATING: 600 volts (rms) at sea level CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz JACKET COLOR: White preferred JACKET ELONGATION AND TENSILE STRENGTH: Elongation, 50% (minimum) Tensile Strength, 5000 lbf/in<sup>2</sup> (minimum) JACKET FLAWS: Spark Test, 1000 volts (rms) Impulse Dielectric Test, 6.0 kV (peak) SHIELD COVERAGE: 85% (minimum) (each) SHIELD RESISTANCE (Finished Cable): 12 milliohms/meter (maximum) VOLTAGE WITHSTAND (Post Environmental): 1000 volts (rms), 60 Hz, 1 minute

CABLE IDENTIFICATION: Mark outer jacket surface in a contrasting color at 12 inch (nominal) intervals as follows: " 55PC6021-AWG \*\* " \*\* = Applicable Manufacturer CAGE code as follows: 06090 = Menlo Park, CA SU473 = Tijuana, MX

PART NUMBER:

The "\*" in the part numbers on page 1 shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

<u>1</u>/ Example: AWG 22, red and blue component wires; white jacket: 55PC6021-22-2/6-9

1/ See footer section on page 1