


2	—	2	—	—	1-18023-3	SCR, SHC, M4X16	70
2	—	2	—	—	18024-6	SCR, BHC, M4X8	69
1	—	1	—	—	2168489-1	ACTUATOR, SPARE MCI	68
1	—	1	—	—	2161273-1	GUARD, END FEED INSERT	67
1	—	1	—	—	2161272-2	GUARD, END FEED	66
—	—	1	1	—	460277-1	AIR FEED ASSY	65



							39
							38
-	-	-	-	-	-	-	37
-	-	-	-	-	-	-	36
-	-	-	-	-	-	-	35
							34
							33
							32
							31

—	—	1	1	—	1424330-1	GUIDE, TERMINAL	16
—	—	1	1	—	1424334-1	REAR STRIPPER	15
—	—	1	1	—	27058-2	PLUNCER, SPRING, STUBBY	14
—	—	1	1	—	21004-9	SCR, SHLD .31 DIA X .50 LG.	13
—	—	1	1	—	1338124-1	WHEEL, ADJUSTING	12
—	1	1	1	—	1424319-7	ANVIL	11
—	—	1	1	—	1424335-2	SHEAR	10
—	—	1	1	—	458409-2	HOLDER, SHEAR	9
—	—	1	1	—	6-22282-8	SPRING, SHEAR RETURN	8
—	—	1	1	—	1424322-1	BLOCK, SHEAR DEPRESSOR	7
							6
—	—	1	1	—	1338212-1	HOLDER, TOOL	5
—	—	1	1	—	690461-4	SCREW, SHEAR STOP	4

[illegible]

DIMENSIONS IN INCHES. DO NOT SCALE PRINT.		MATL		—		HT TR		—		FIN		—	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		DR		12/10/00		APP		12/10/00		 TE Connectivity Harrisburg, PA 17105-3608			
2 PLC DEC ±.25		B.HIGMAN						T.ELBIN					
3 PLC DEC ±.1		CHK		12/10/00		REL		—					
4 PLC DEC ±.1		B.HIGMAN											
ANGLES ±.1		NAME		EF THRU SPLICE APPL						MACHINE REF			
SURF TEXTURE: ✓		SCALE		—		DWG NO		566405		SHEET		REV	
REMOVE BURRS, BREAK SHARP EDGES R.015 MAX				D						1 OF 1		E2	
CAGE CODE 00779		CUSTOMER AND ASSEMBLY DRAWING 1								RESTRICTED TO			

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	, 19
------------------------------	--------------------------	------

RELEASED FOR PUBLICATION	ALL RIGHTS RESERVED.
--------------------------	----------------------

THIS DRAWING IS U
© COPYRIGHT 19

AMP 1756 REV 3-92 Translated: 07/03/21 23:17:02 from MMDB.HMMMS6 / rpn
Computerision, Inc., 4400 University Ave. #1000 TE559482

1

100

1

1

[illegible]

10

TO