



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	REVISED PER CM-1754	17AUG1988	PKC	RS
	H1	REVISED PER ECN-23-233438	02OCT2023	WLS	VS



NOTES:

- FOR ADDITIONAL INFORMATION SEE DRAWING 350079.
- THIS TERMINAL TO BE SUPPLIED IN INDIVIDUAL FORM, NOT AS A CONTINUOUS STRIP.
- .000030 THK GOLD INSIDE OF WIRE BARREL & ON THE TIP OF PIN; REMINDER OF CONTACT IS NICKEL PLATED.
- DIMENSIONS IN BRACKETS ARE IN INCHES.



.040-.075 OR (2) .040 MAX	30-22	GOLD	.012 BRASS	61174-5
.040-.075 OR (2) .040 MAX	30-22	TIN	.012 BRASS	61174-1
INSULATION RANGE	WIRE SIZE	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. R. KUNKLE 06APR1967	TE Connectivity NAME PIN, LOOSE PIECE COMMERCIAL MATE-N-LOK -		
DIMENSIONS: mm [INCHES]		CHK J. R. KUNKLE 10APR1967			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W. PANYA 17APR1967	PRODUCT SPEC 108-1000		
0 PLC ±- 1 PLC ±- ±0.38 [.015] 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±1°0'		APPLICATION SPEC 114-1012	SIZE A3	CAGE CODE 00779	DRAWING NO C-61174
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT -	RESTRICTED TO -		
CUSTOMER DRAWING			SCALE 10:1	SHEET 1 OF 1	REV H1