



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B1		ECO-20-017273	10DEC2020	RR	SZ



- 1 FOR USE WITH .093 MINIMUM THICK PRINTED CIRCUIT BOARD, REFER TO APPLICATION SPECIFICATION FOR PRINTED CIRCUIT BOARD LAYOUT DIMENSIONS AND FINISH RECOMMENDATIONS.
- 2 MATERIAL:
HOUSING: GLASS-FILLED NYLON OR POLYESTER UL94V-0 RATED, COLOR: BLACK.
CONTACTS: COPPER ALLOY.
INSERTS: BRASS.
- 3 FINISH:
CONTACTS: .000030 MINIMUM GOLD IN MATING AREA, .000100 MINIMUM TIN ON COMPLIANT PIN, ALL OVER .000050 MINIMUM NICKEL.
-OR-
GOLD FLASH OVER PALLADIUM-NICKEL, .000030 MINIMUM TOTAL IN MATING AREA, .000100 MINIMUM TIN ON COMPLIANT PIN, ALL OVER .000050 MINIMUM NICKEL.
INSERTS: UNPLATED.

OBSOLETE

5745465-2
PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009.			DWN: C. PETERS/DTL CHK: S. BOLASH	04FEB06 04FEB06	 TE Connectivity					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: M. WALMSLEY	04FEB06	NAME	RECEPTACLE ASSEMBLY, ACTION-PIN, 25 POSITION, HD-20, AMPLIMITE			
		0 PLC ± .		PRODUCT SPEC		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
		2 PLC ± .		108-40014						
		3 PLC ± .05		APPLICATION SPEC						
4 PLC ± .		± .		114-40026						
MATERIAL		FINISH		WEIGHT		A1		00779	5745465	-
				CUSTOMER DRAWING		SCALE		4:1	SHEET	1 OF 1
										REV
										B