



| LOC | DIST | REVISIONS |     |                           |         |      |
|-----|------|-----------|-----|---------------------------|---------|------|
| AF  | 50   | P         | LTR | DESCRIPTION               | DATE    | DWN  |
|     |      |           | K3  | REVISED PER ECR-11-006644 | 05APR11 | HMR  |
|     |      |           |     |                           |         | APVD |
|     |      |           |     |                           |         | GJ   |



- 1 CONTINUOUS STRIP ON REELS.
- 2 TIN PLATE OVER COPPER UNDERPLATE.
- 3 WIRE RANGE FOR NEW APPLICATIONS: 1.27–2.38mm<sup>2</sup>[2500–4700 CMA] (WIRE RANGE APPROVED FOR APPLICATIONS IMPLEMENTED PRIOR TO 2005: 2000–5300 CMA).
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 5 CRIMP WIDTH:3.05[.120] F TYPE. CRIMP HEIGHT IN INCHES (+/-.002)=(TOTAL CMA OF WIRES + 12240)/220000.



|                                        |        |                                                                        |                 |               |
|----------------------------------------|--------|------------------------------------------------------------------------|-----------------|---------------|
| 4 OBSOLETE                             | —      | H02 COPPER NICKEL                                                      | 3               | 61492-3       |
|                                        | 2      | 082 BRASS                                                              | 3               | 61492-2       |
|                                        | —      | 082 BRASS                                                              | 3               | 61492-1       |
|                                        | FINISH | MATERIAL                                                               | WIRE RANGE      | PART NUMBER   |
| THIS DRAWING IS A CONTROLLED DOCUMENT. |        | DWN<br>MICHAEL S. FEHER<br>CHK<br>STEVE HEADER<br>APVD<br>STEVE HEADER | TE Connectivity |               |
| DIMENSIONS:<br>mm [INCHES]             |        | TOLERANCES UNLESS OTHERWISE SPECIFIED:                                 | NAME            |               |
|                                        |        | 0 PLC ± —                                                              | SPLICE          |               |
|                                        |        | 1 PLC ± —                                                              |                 |               |
|                                        |        | 2 PLC ± 0.25[.010]                                                     |                 |               |
| MATERIAL                               |        | FINISH                                                                 | SIZE            | RESTRICTED TO |
| SEE TABLE                              |        | SEE TABLE                                                              | 114-2088        | —             |
|                                        |        | WEIGHT                                                                 | SCALE           | REV           |
|                                        |        | CUSTOMER DRAWING                                                       | 10:1            | K3            |