



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
IS	-		A	FIRST ISSUE	13JAN2006	MG


- 1) Dimensions of mating face according to IEC 169-29 and CECC 22230
- 2) Full Crimp version : Center conductor 8 indent pos.5
Outer conductor hex 6.8±0.05
See Tyco application spec. 114-90009
- 3) DIN ISO 8015 ; DIN ISO 2768-mH
- 4) Packaging : 200 pieces per box.
Body and loose parts seperately packed into plastic bags.



Cable preparation for cable type LMR-240 FR



Cross reference table					
Part number	Cable type	Description	Material	Plating	Packaging
619224-1	LMR-240 FR	Body	Brass	1 µm Au min in contact area	4
		Center conductor	CuBe / CuZn	1 µm Au min in contact area	
		Dielectric	PTFE	-	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN R. Luppi	23MAR2005	tyco Electronics		Tyco Electronics Lugano - Switzerland	
		CHK D. Bozzer	23MAR2005				
		DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -			
MATERIAL -		FINISH -		APPLICATION SPEC 114-90009		RESTRICTED TO -	
				WEIGHT -		SIZE A3	
						CAGE CODE 00779	
						DRAWING NO C= 619224	
				CUSTOMER DRAWING		SCALE 5/1	
						SHEET 1 OF 1	
						REV A	