

DESCRIPTION	MATERIAL	FINISH
MODULE ASSEMBLY	EPOXY	COLOR: BLACK
GROMMET	FLUORSILICONE RUBBER	COLOR: BLUE
CONTACT SOCKET	BERYLLIUM COPPER PER QQ-C-533	GOLD PLATE PER MIL-G-45204
RETAINING CLIP	BERYLLIUM COPPER PER QQ-C-533 OR STAINLESS STEEL PER QQ-S-766	NONE
CONTACTS	COPPER ALLOY PER MIL-C-39029/1	GOLD PLATE PER MIL-G-45204
SEALING PLUGS	F.E.P. PER MIL-P-19468	COLOR: BLACK

REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
F		REVISED PER ECN-23-218303	19JUN2023	AG	FN

D

C

B







A

D

C

B




A



(30)

(31)




(32)



(33)

(34)




(35)



(36)

(37)




(38)



(39)

(40)


(42)



(43)

(44)

(45)




(46)

BUSSING ARRANGEMENTS

BUSSING ARRANGEMENT OUTLINE DENOTES INTERNAL ARRANGEMENT OF CONTACT SOCKETS.

MODULE ASSEMBLY MARKED WITH CUSTOMER PART NO., MILITARY PART NO. IF REQUIRED .060 MINIMUM HIGH CHARACTERS AT APPROXIMATE AREA SHOWN.

MODULE ASSEMBLY MARKED WITH "TE", TE PART NO. AND DATE CODE .060 MINIMUM HIGH CHARACTERS AT APPROXIMATE AREA SHOWN.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MECK 3-10-93		 TE Connectivity									
		CHK R. RYAN 3-31-93											
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME									
	0 PLC ± -		APVD R. RYAN 3-31-93		MODULE ASSY, FEED-BACK, SIZE 21, TJ								
	1 PLC ± -		PRODUCT SPEC										
	2 PLC ± -		-										
	3 PLC ± -		APPLICATION SPEC										
	4 PLC ± .005		-										
ANGLES ± -		-		SIZE		CAGE CODE	DRAWING NO		RESTRICTED TO				
MATERIAL		FINISH		WEIGHT		A2 00779		C-592629		-			
-		-		0									
CUSTOMER DRAWING						SCALE		2:1		SHEET	1 OF 2	REV	F

