


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
IS	-		51	First issue	25JUL2007	AM	DB
			A	Released to production	23JUL2008	MG	DB

Partial section B-B




3D view
5:1




- 1 GENERAL TOLERANCES: ISO 2768-m-H
- 2) Items 1 and 2 packaged unassembled
- 3) Item 4 is not visible


619336-1	5	1	Cap	Brass	min. 0.1 µm Au over min. 2 µm NiP
	4	1	Dielectric	PTFE	-
	3	1	Retaining Ring	BeCu/ Bz4	min. 0.1 µm Au over min. 2 µm NiP
	2	1	Body	Brass	min. 0.1 µm Au over min. 2 µm NiP
	1	1	Center Con.	Brass	min. 0.1 µm Au over min. 2 µm NiP
TE Nr	Item	Qty	Description	Material	Plating



Recommended cable strip length.



1:1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN A. Mariotti 25JUL2007		 Tyco Electronics tyco Electronics Lugano (Switzerland)					
		CHK D. Bozzer 25JUL2007							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MMCX right angle cable plug for cable RG 405					
		APVD -							
		PRODUCT SPEC 108-71075							
		APPLICATION SPEC 114-71040							
		WEIGHT -							
		SIZE A3							
MATERIAL -		FINISH -		CAGE CODE 00779		DRAWING NO C-619336		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 10:1		SHEET 1 OF 1			