



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASED	27JUL2020	GK	OD

NOTES:


- 1 MATERIAL: COPPER-ZINC LEAD ALLOY
FINISH: f1Cu+Ni2Au0.2µm PASSIVATED
- 2 PLATING THICKNESS MEASUREMENT POINT



SECTION A - A



0.35 - 1.5 mm ²	5	61.117.11	61-0117-011-000
CRIMPING RANGE	WEIGHT (g) REF	INTERCONTEC P/N	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 27JUL2020 GOPALAKRISHNA HV		 TE Connectivity									
DIMENSIONS: mm		CHK 27JUL2020 ONDREJ DUSAN											
		APVD 27JUL2020 ONDREJ DUSAN		NAME CONTACT PIN 1.6 MM, CRIMPING RANGE 0.35 - 1.5 MM2									
		TOLERANCES UNLESS OTHERWISE SPECIFIED: <table><tr><td>0 PLC</td><td>±</td></tr><tr><td>1 PLC</td><td>±</td></tr><tr><td>2 PLC</td><td>±</td></tr><tr><td>3 PLC</td><td>±</td></tr><tr><td>4 PLC</td><td>±</td></tr><tr><td>ANGLES</td><td>±0° 30'</td></tr></table>				0 PLC	±	1 PLC	±	2 PLC	±	3 PLC	±
0 PLC	±												
1 PLC	±												
2 PLC	±												
3 PLC	±												
4 PLC	±												
ANGLES	±0° 30'												
MATERIAL 		FINISH 		SIZE A3	CAGE CODE 00779								
		PRODUCT SPEC -		DRAWING NO C-61-0117-011-000	RESTRICTED TO -								
		APPLICATION SPEC -											
		WEIGHT SEE TABLE											
CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1								
				REV A									