




LOC	DIST	REVISIONS				
CF	39	REV	DESCRIPTION	DATE	OWN	APVD
		A	REV 8 REDRAWN PER ECOB20-0995-95	12-6-95	LM	CA
		B	REV PER OB20-0326-96	4-19-96	TS	GG
		C	REV PER OB20-0909-96	10-11-96	TS	GG
		D	ADD -7 OB20-1153-96	12-6-96	TS	GG
		E	REV PER OS20-0262-02	14MAY02	TS	CA



- 1 EACH HOUSING CONTAINS 5 SOCKET CONTACTS. CONTACTS ARE PLATED WITH .00038 MIN THICK GOLD OVER .00127 MIN THICK NICKEL.
- 2 ADDITIONAL TIE TAPE PLACED ON CABLE BUNDLE, SPACED EVERY 625 mm MAX.
- 3. MAXIMUM ALLOWABLE MATING POST LENGTH 8.5mm
- 4. CABLE : SIGNAL & DRAINS 28 AWG SOLID  
 PROPAGATION DELAY 4.265 NS/METER NOM  
 IMPEDANCE 100 OHMS DIFFERENTIAL NOM  
 JACKET PVC - UL RECOGNITION



WIRING DIAGRAM

10000.0±125.0	621275-7
1500.0±25.0	621275-6
5000.0±75.0	621275-5
4000.0±50.0	621275-4
3000.0±50.0	621275-3
2000.0±25.0	621275-2
1000.0±20.0	621275-1
DIM L	PART NUMBER

<small>THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING DEPARTMENT SHALL BE CONTACTED FOR THE LATEST REVISION.</small>		DWN <b>L. MORNINGSTAR</b> 12-6-95 CHK C. ADAMS 12-6-95 APVD C. ADAMS 12-6-95	<b>AMP</b> AMP Incorporated Harrisburg, PA 17105-3608
DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-	PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING	NAME CABLE ASSEMBLY, 1 x 5, 100 OHM, 2mm HM SIZE A1 CAGE CODE 00779 DRAWING NO 621275 SCALE 4:1 SHEET 1 OF 1 REV E