




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
P1		REVISED PER ECO-12-13810	13SEP2012	JR	TM
P2		REVISED PER ECN-23-233438	02OCT2023	WLS	VS



NOTES:

1. REFER TO AMP SPEC. TEC-108-1015 FOR TERMINATION REQUIREMENTS.
2. WIRE RANGE: 0.2 - 0.9mm<sup>2</sup> [24 - 18 AWG].
3. INSULATION RANGE: 2.54[.100] MAX DIA.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.

PRE-TIN	0.30[.012] BRASS	61527-2
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. BECK 28JAN1993												
DIMENSIONS: mm [INCHES]		CHK R. SWING 28JAN1993												
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. MARTIN 10FEB1993												
<table border="0"> <tr><td>0 PLC</td><td>±-</td></tr> <tr><td>1 PLC</td><td>±-</td></tr> <tr><td>2 PLC</td><td>±0.25[.010]</td></tr> <tr><td>3 PLC</td><td>±-</td></tr> <tr><td>4 PLC</td><td>±-</td></tr> <tr><td>ANGLES</td><td>±1°</td></tr> </table>		0 PLC			±-	1 PLC	±-	2 PLC	±0.25[.010]	3 PLC	±-	4 PLC	±-	ANGLES
0 PLC	±-													
1 PLC	±-													
2 PLC	±0.25[.010]													
3 PLC	±-													
4 PLC	±-													
ANGLES	±1°													
MATERIAL SEE TABLE	FINISH SEE TABLE	APPLICATION SPEC 114-1012	NAME PIN COMMERCIAL MATE-N-LOK	RESTRICTED TO										
		WEIGHT -	SIZE A3	CAGE CODE 00779										
		CUSTOMER DRAWING	DRAWING NO G-61527	SCALE 5:1										
			SHEET 1 OF 1	REV P2										