






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AC1	REVISED PER ECR-25-240132	07APR2025	JZ	TD




- 1 CONTINUOUS STRIP ON REEL.
- 2 WIRE SIZE IS 0.82-1.31MM² [#18-#16 AWG].
- 3 INSULATION RANGE IS 1.50-2.62 [.059-.103] DIA.
- 4 ADDITIONAL PERFORMANCE REQUIREMENTS APPLY. CONSULT TE PRODUCT ENGINEERING FOR SPECIFICS.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 6 QTY/REEL : 8500 PCS
- 7 QTY/REEL : 17000 PCS

0.406±0.025
[.016±.001]

5 OBSOLETE

H03 TIN-BRASS.	POST TIN PLATED	6 6-62131-3
H03 TIN-BRASS.	-	6 62131-8
COPPER ALLOY	POST TIN PLATED	4 62131-7
H03 PHOS BRONZE	POST TIN PLATED	4 7 62131-6
H03 TIN-BRASS.	-	7 62131-5
H03 TIN-BRASS.	POST TIN PLATED	7 62131-3
MATERIAL		FINISH
		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 20/JAN/95 PHILLIP M FORTNEY	 TE Connectivity				
		CHK 20/JAN/95 JEFF R RUTH					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 20JAN95 R KUZO	NAME RECEPTACLE, CLUSTER PIN, 2.29 [.090] DIA —				
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.25 [.010] 3 PLC ± — 4 PLC ± — ANGLES ± —	PRODUCT SPEC 108—2008					
MATERIAL	FINISH	APPLICATION SPEC 114—2019	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
SEE TABLE	SEE TABLE	WEIGHT —	A3	00779	C—62131	—	
CUSTOMER DRAWING					SCALE	SHEET	REV
					4:1	1 OF 1	AC1