






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
IS	-		51	First issue	27FEB07	AN	DB
			53	Update drawing	30AUG07	AM	DB
			A	Released to production	22JUL2008	MG	DB
			B	New cap	10MAR2010	MS	MG



- 1 Interface according to MIL-STD-348A.
Characteristic impedance 50 Ohm.
- 2 General tolerances acc.to ISO 2768-mH
- 3) Bulk packaging.

619303-2	4	1	Cap	Brass	min. 2 µm CuSnZn	1
	3	1	Dielectric	PTFE	-	1
	2	1	Cent. conductor	CuBe	min. 0.1µm Au over min. 2 µm NiP	1
	1	1	Body	CuBe	min. 0.1µm Au over min. 2 µm NiP	1
Part Nr	Item	Qty	Description	Material	Plating	Qty

STRIPPING DIMENSIONS



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN A.Nicolini 27FEB2007	Tyco Electronics tyco Electronics CH-Switzerland-Lugano	
DIMENSIONS: mm		CHK D.Bozzer 27FEB2007	NAME SMP Plug 90° Cable Solder RG405	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	SIZE A3	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		PRODUCT SPEC 108-71081 APPLICATION SPEC 114-71040 WEIGHT -	DRAWING NO C-619303	
MATERIAL -		RESTRICTED TO -		SCALE 20:1
		SHEET 1 OF 1		REV B