













- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59 ± 0.08 [$.220 \pm .003$] CENTERS.
- 2 SLOT ACCEPTS A $0.61 - 0.81\text{mm}$ [#22.5 - #20 AWG] SINGLE OR 0.61mm [#22.5 AWG] DOUBLE COPPER MAGNET WIRE ONLY. SLOT ACCEPTS A $0.68 - 0.91\text{ mm}$ [#21.5 - #19 AWG] SINGLE OR 0.68 mm [#21.5 AWG] DOUBLE ALUMINUM MAGNET WIRE ONLY. ALUMINUM WIRE RANGE APPLIES FOR POST-TIN PLATED VERSIONS ONLY.
- 3 POKE-IN ACCEPTS A $0.81 - 1.02\text{mm}$ [#20 - #18] AWG SOLID OR FUSED STRANDED LEAD WIRE.
- 4 0.0010 [.000040] MIN TIN.
- 5 VARNISH RESIST OVER 0.0010 [.000040] MIN TIN.
- 6 SPECIAL REEL QUANTITY FOR SPAIN PRODUCTION ONLY.
- 7 PRELIMINARY - NOT FOR PRODUCTION.
- 8 SUITABLE FOR COPPER MAGNET WIRES ONLY
- 9 PART IS REELED WITH PAPER INTERLEAVE.

	REVERSE	PAPER	CARDBOARD REEL	BRASS		1-62420-2
		SPLICE FREE	CARDBOARD REEL	BRASS		1-62420-8
	STANDARD	WELD	CARDBOARD REEL	PHOSPHOR BRONZE		1-62420-4
	STANDARD	PAPER	CARDBOARD REEL	BRASS		62420-9
	REVERSE	PAPER	CARDBOARD REEL	BRASS		 62420-6
OBSOLETE	STANDARD	SPLICE FREE	PLASTIC REEL	BRASS		 62420-5
OBSOLETE	STANDARD	WELD	CARDBOARD REEL	PHOSPHOR BRONZE		62420-4
OBSOLETE	STANDARD	WELD	CARDBOARD REEL	BRASS		62420-3
OBSOLETE	STANDARD	WELD	CARDBOARD REEL	BRASS		62420-2
	STANDARD	PAPER	CARDBOARD REEL	BRASS		62420-1
REMARKS	REELING DIRECTION	SPLICE	REELING MATERIAL	MATERIAL	FINISH	PART NO.