





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	W3	REVISED PER ECR-24-228254	11MAR2025	DB	RE




VIEW A-A



SECTION B-B

- 1
- CONTINUOUS STRIP ON REELS
- 2
- 0.00381 [.000150] MIN TIN PL
OVER 0.00254 [.000100] MIN
COPPER PL.
- 3
- PARTS TO MEET AMP SOLDERABILITY
SPEC 109-11-2, MIDLY ACTIVATED
ROSIN.
- 4
- PRINTED CIRCUIT BOARD THK IS
0.81/2.36 [.032/.093] THK WITH A
HOLE DIA OF 1.70/1.60 [.067/.063].
- 5
- FINISH LEAD-FREE, MATTE TIN
PLATING OVER COPPER OR NICKEL
UNDER-PLATING.

OBSOLETE	5	61968-6
	2	61968-1
NOTE	FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 22FEB01		TE Connectivity						
		CHK MS FEHER 22FEB01								
DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.25 [.010] 3 PLC ± — 4 PLC ± — ANGLES ± —		APVD N DEIBERT 22FEB01		NAME TAB, FASTON, PC BOARD 2.79 [.110] SERIES				
				PRODUCT SPEC —						
		APPLICATION SPEC —		SIZE A3	CAGE CODE 00779			DRAWING NO C-61968	RESTRICTED TO —	
		WEIGHT 0.000000								
MATERIAL BRASS		FINISH 		CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1	REV W3