


LOC	DIST	REVISIONS				
CF	39	P	LTR	DESCRIPTION	DATE	APVD
			A	REVISION PER ECO-05-006188	29JUN05	DW



- NOTES:
1. WRAP FOIL OVER PRE-MOLD 360° FROM CONNECTOR SHELL TO SHELL, IF USING ALUMINUM MYLAR FOIL, ALUMINUM MUST BE FACING INWARD.
 2. PACKAGED IN PRINTED ZIPLOCK POLYBAG.
 3. LABEL ON POLYBAG TO READ AS FOLLOWS:

621823-1
DB9M/F GENDER CHANGER
 4. THIS PRODUCT IS PRODUCED IN COMPLIANCE WITH ANSI/ASQC Z1.4-1993, TO AN INSPECTION LEVEL III, WITH A NORMAL SAMPLING PLAN.
 5. TEST REQUIREMENT:
CONTINUITY RESISTANCE: 1 ohm MAX,
INSULATION RESISTANCE: 50 M ohm MIN.
HI-POT TEST: DC 300V/0.01 Sec MIN.
 6. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ENVIRONMENTAL STANDARD 230-702.

TYCO P/N: 621823-1

P1	P2
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
SHELL	SHELL

1	PC	DB9 FEMALE, SOLDER TYPE, CONTACT: GOLD FLASH, SHELL: NICKEL PLATED, INSULATION COLOR: BLACK.	8
AR	MR	UL1007 28AWG, COLOR: BLACK.	7
AR	MR	ALUMINUM FOIL, W: 30.0MM.	6
AR	KG	INNER MOLD PE.	5
AR	KG	MOLD PVC, 40P, COLOR: BEIGE(BG01).	4
4	PC	#4-40 ALL METAL SCREW, W/WASHER.	3
4	PC	#4-40 HEX NUT, 5.0*6.0MM.	2
1	PC	DB9 MALE, SOLDER TYPE, CONTACT: GOLD FLASH, SHELL: NICKEL PLATED, INSULATION COLOR: BLACK.	1
QTY	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.EISENTRAU	12-4-96	tyco Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
		CHK R.CAPP	12-10-96			
DIMENSIONS: mm		APVD D.WILSON	12-4-96	NAME GENDER CHANGER, DB9, MALE/FEMALE		
		PRODUCT SPEC				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		WEIGHT				
MATERIAL		FINISH		A3 00779 C-621823		
				CUSTOMER DRAWING		
				SCALE	1:1	
				SHEET	1 OF 1	
				REV	A	