



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
		B1		REVISED PER ECR-09-002564	12FEB09	HMR	KR

IDENTIFICATION NUMBER FOR MAGNET WIRE RANGE



- 1 AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR POTTED-IN TO PREVENT PULL OUT WHEN MATING RECEPTACLE IS DISCONNECTED.
- 2 SLOT ACCEPTS A SINGLE WIRE ONLY OF 1.09-1.29mm [#17.5-#16] AWG COPPER MAGNET WIRE.
- 3 VARNISH RESIST OVER 0.002032 [.000080] MIN TIN.

LOOSE PIECE	63599-1
TYPE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.S. FEHER 10/10/90	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK P. FORTNEY 10/12/90		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. RANDOLPH 10/19/90	NAME	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-2012	TAB, 4.75 [.187] FASTON,™ MAG-MATE™	
MATERIAL H03 HARD BRASS		FINISH	APPLICATION SPEC 114-2066	RESTRICTED TO
			WEIGHT -	
			SIZE A3	CAGE CODE 00779
			DRAWING NO C-63599	
			SCALE 4:1	SHEET 1 OF 1
			CUSTOMER DRAWING	REV B1