





REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
	BI	REVISED PER ECN-25-320055	06MAY2025	TR	RK



1. TERMINAL: PCT POLYESTER, BLACK, UL 94V-0.
2. TERMINAL: 0.305 THICK PHOS BRONZE PLATED WITH 1.27µm MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND 0.03µm MINIMUM THICK MATTE TIN IN SOLDER AREA OVER 0.27µm MINIMUM THICK NICKEL UNDERPLATE.
3. SHIELD: 0.01µm THICK COPPER ALLOY PLATED WITH 0.27µm MINIMUM THICK NICKEL AND 2.03µm MINIMUM HOT TIN DIP ON REAR GROUND TABS.
4. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 15 SUBPART F.
5. DRILL HOLES ONLY REQUIRED FOR 6339168-1.
6. USE #30 FLANK BIT OR EQUIVALENT DRILL BIT WHEN PRODUCING DRILL HOLES.
7. RECOMMENDED APPLICATIONS: FAST ETHERNET, BASE-T ETHERNET, AND 10/100 BASE-T ETHERNET (CAT 5 TWO PAIR, 2, 3/6).



SCALE 2:1

OBSOLETE	NONE	6339168-2
OBSOLETE	3	6339168-1
	REAR PCB TABS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA CHK J. WESTMAN APVD S. FLICKINGER	23JUN2005 DOCKS 23JUN2005 23JUN2005	NAME ASSEMBLY, STACKED JACK, 2X4, 8 POSITION, SHIELDED, WAVE PANEL GROUND	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-1163-9	
		0 PLC ±.25 1 PLC ±.25 2 PLC ±.25 3 PLC ±.25 4 PLC ±.25 ANGLES ±.5 FINISH		APPLICATION SPEC 114-2048	
MATERIAL -		WEIGHT -		SIZE A	
CUSTOMER DRAWING		SCALE 2:1		SHEET 1 OF 2	
				REV BI	

