

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,2005.

© COPYRIGHT 2005 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
J

DIST

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD

A


RELEASED

07DEC05

T.T

Y.Y

-1 ; AS SHOWN

M2 SCREW POST
(WITH NYLOK)


MOUNTING SURFACE

4.1
0.8


5.5

Ø1.5
±0.1
Ø3

0.7

0.5 REF
SHELL
GROUND
(2PLACES)+0.1
1.501.75
0.355
5BUTTON COLOR
:BLACKTABLE
表 1

POST LENGTH	5	3.5	4.25
回路番号 CIRCUIT NO.	1,17,34,35,51,68	36,67	その他 OTHERS



0.6mm PITCH CARD EDGE CONNECTOR FOR THIS CARDBUS PRODUCTS	
PARTS NUMBER	DESCRIPTION
6123215-1	HARD TRAY ASSY
6376045-1	ON TAPING(EMBOSS)

2	SPRING PIN	④
4	NUT (M2)	③
1	EJECTOR SUB ASSEMBLY	②
1	HEADER MAIN ASSEMBLY	①
数量 QTY	名称 NAME	ITEM

- ① ポスト長は表 1を参照の事。
- 2 推奨ネジ締め付けトルク: 0.15N・m(1.5kgf・cm)から0.2N・m(2kgf・cm)
- 3 適応PCカード: PCMCIA準拠のPCカード
- 4 本製品は6ヶ所ネジ止めする(2 OF 2 参照)
- 5 ネジの締め付け時のナット押し付け力: 14.7N(1.5Kg)以下
- ① REFER TO TABLE 1 FOR POST CONTACT LENGTH.
- 2 RECOMMENDED TIGHTENING TORQUE
:FROM 0.15N・m(1.5kgf・cm) TO 0.2N・m(2kgf・cm)
- 3 APPLIED CARD: PCMCIA ATTRIBUTE PC CARD.
- 4 THIS PRODUCT IS FIXED 6 PLACE WIHE SCREWS (SEE 2 OF 2)
- 5 THE AXIAL FORCE TO NUTS WHEN MOUNTING CARDBUS: 14.7N(1.5Kg) MAX

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.TSUZAKI 25NOV05	tyco Electronics Tyco Electronics AMP K.K. Kawasaki, Japan	
DIMENSIONS: 単位: 耗 mm		CHK T.FUTATSUGI 07DEC05		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD Y.YA.MAMOTO 07DEC05	NAME 名称	
0 PLC ± 0.5 1 PLC ± 0.5 2 PLC ± 0.5 3 PLC ± 0.5 4 PLC ± 0.5 ANGLES ± -		PRODUCT SPEC 製品規格 108-78192	CARD BUS DOUBLE SLOT BOTTOM MOUNT PUSH-PUSH TYPE	
MATERIAL 材料		APPLICATION SPEC 取付適用規格	SIZE A3	CAGE CODE 00779
FINISH 仕上		WEIGHT 25.7gr	DRAWING NO 番号 C-6376932	RESTRICTED TO
CUSTOMER DRAWING		SCALE 尺度 1:1	SHEET 1 OF 2	REV A

4

3

2

1

