


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - TE CONNECTIVITY ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	C3	REVISED PER ECR-19-001960	06FEB2019	BDA SV

IDENTIFICATION NUMBER FOR MAGNET WIRE RANGE




1 FOR MAG-MATE CAVITY SPECIFICATION

2 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON .330 CENTERS.

3 AFTER INSERTION INTO PLASTIC HOLDER MAG-MATE MUST BE POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.

4 TWO WIRES OF THE SAME SIZE MAX PER SLOT.  
 #22-#20 AWG COPPER MAGNET WIRE RANGE.  
 #21-#19 AWG AL MAGNET WIRE RANGE



63495-1  
 PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.S. FEHER 5/19/88	TE Connectivity		
DIMENSIONS: INCHES		CHK P. FORTNEY 5/31/88			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J SWARTZ 5/31/88	TAB, .250 FASTON,™ MAG-MATE™		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .010 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-2053	RESTRICTED TO		
MATERIAL BRASS		APPLICATION SPEC 114-2066 1	SIZE A3	CAGE CODE 00779	DRAWING NO C-63495
FINISH VARNISH RESIST, SYNTHETIC OIL OVER TIN		WEIGHT	SCALE 4:1		SHEET 1 OF 1
		CUSTOMER DRAWING	REV C3		