






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER ECO-10-012356	16DEC2010	CJV	EJB
C		ECO-15-006497	18APR2016	LL	SH

- 1 HOUSINGS; POLYESTER, UL 94V-O RATED, NATURAL
SIGNAL AND SIGNAL GROUND CONTACTS: COPPER ALLOY
UTILITY CONTACTS: PHOSPHOR BRONZE
- 2 UTILITY CONTACTS: 0.76um MIN GOLD IN CONTACT AREA,
2.54um MIN TIN ON PCB TAILS, OVER 1.27um MIN NICKEL OVER ALL.
SIGNAL AND SIGNAL GROUND CONTACTS: 0.76um MIN GOLD IN CONTACT AREA,
2.54um MIN TIN ON PCB TAILS, OVER 1.27um MIN NICKEL OVER ALL.
3. ROWS A, C, D, AND F ARE SIGNAL CONTACTS. ROWS B AND E ARE SIGNAL GROUND CONTACTS.
- 4 CONNECTOR SIZE CAN ACCOMMODATE INDICATED QUANTITY OF DIFFERENTIAL PAIRS.
- 5 DIMENSIONS PER CUSTOMER BOARD LAYOUT.
- 6 COMPANY LOGO IN APPROXIMATE AREA SHOWN.
- 7 OBSOLETE PART.



224	107.24	100.54	88.90	88.39	72	6367690-9
200	97.08	90.38	78.74	78.23	64	6367690-8
176	86.92	80.22	68.58	68.07	56	6367690-7
152	76.76	70.06	58.42	57.91	48	6367690-6
128	66.60	59.90	48.26	47.75	40	6367690-5
104	56.44	49.74	38.10	37.59	32	6367690-4
80	46.28	39.58	27.94	27.43	24	6367690-3
56	36.12	29.42	17.78	17.27	16	6367690-2
32	25.96	19.26	7.62	7.11	8	6367690-1
N	H DIM	D DIM	B DIM	A OR C DIM	DIFF PAIRS 4	PART NUMBER

SPACING TO ADAPTER BOARD
CONNECTOR PIN A1 LOCATION

RECOMMENDED PC BOARD FOOTPRINT
COMPONENT SIDE SHOWN
SCALE:5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: WM VAN SCYOC 08JUN05	 TE Connectivity				
DIMENSIONS:		CHK: N. REESER 08JUN05					
mm		APVD: W. REESER 08JUN05	NAME		Z-DOK+ HOST BOARD CONNECTOR ASSEMBLY, 8-72 SIGNAL DIFF. PAIR, 1 UTILITY CONTACTS PER SIDE		
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
		0 PLC ±.3		108-1985			
		1 PLC ±0.25		APPLICATION SPEC			
		2 PLC ±.1		114-13068			
MATERIAL		FINISH		SIZE CASE CODE DRAWING NO		RESTRICTED TO	
1		2		A1 00779C-6367690			
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 OF 1 REV C	